



keep it humming™

Vertiv™ PowerIT



Future-Ready
Flexibility



Upgradeable
Monitoring




Scalable
Intelligence



Adapts to
Your Business



Protects Your
Investment



Enhance business agility, efficiency and availability

- Designed for reliable power distribution and control in data centers and industrial applications.
- Available in a variety of single or three phase electrical and receptacle configurations with different intelligence options.
- Suitable for sophisticated solutions and to address AI and HPC application needs.

 Type	 Receptacles	 Monitoring - IMD-5M:	 Certifications	 Plug Form
• PDU and Rack Transfer Switches (4-8ms with break-before-make process) • Basic, Monitored Unit and Outlet Level, Switched Unit and Outlet level	• Combination Outlet C13/C19 • U-Lock C13, C19 • Regional Outlets • Alternating colorful outlets for phase balancing • Color-coded P-Lock tabs	• LCD auto-rotatable Display • Upgradeable & hot-swappable • Secure boot • Input power with 1% accuracy • Dual 1 Gbps Ethernet • Outputs Remote control • Daisy Chain and Fault-Tolerant • Residual Current Metering • UL2900 cybersecurity certified intelligence • Built in carbon footprint monitoring • Optional environmental monitoring available	• CE Marked • FCC Marked • IEC 62368-1 • EN 55032 • EN 55024 • EN 60950 • RoHS • PSE • Kaycee (KC) • UL / cUL 62368 • RCM	• C14, Schuko (10A, 16A) • IEC60309 (32A, 63A 1 ph & 3ph) • Hardwired >80A • Universal Inputs for worldwide deployments

■ Made-To-Stock (MTS) ■ Build-To-Order (BTO) ■ Configure-To-Order (CTO) ■ Engineer-To-Order (ETO)

KEY HIGHLIGHTS



High Quality
Materials



Premium
Features



Superior
Performance



5 years
warranty

Discover All Configurations

