

KEY FEATURES

- High power density – up to 26.4 kW (12V DC at 2200 A) per shelf in three rack units (5.25")
- Interchangeable rectifiers and battery backup units, each slot accommodates either unit
- Battery backup units that deliver battery backup for 90 seconds or operate in power boost mode to supplement power output of the rectifiers
- Hot swappable – allows for system expansion without disruption
- Expandable – parallel up to three shelves per system for up to 79.2 kW (12V DC at 6600 A) per system
- Operates over a wide AC input voltage range with multiple input configurations
- Safety compliance – UL 60950, CAN/CSA-C22.2 No. 60950-1-03, GR-3160, CE mark, RoHS, REACH

Standard Features

- Ethernet interface to rack management system via SNMP
- System alarming
- Current and power limiting
- Over-voltage protection
- Load sharing
- Over-temperature protection
- Emergency shutdown

Compact, modular design provides a total DC power solution, complete with battery backup, for a wide range of data rack applications.

Description

The modular NetSure™ ITS Series, 12V DC power system provides up to 6600 amps at 12 volts DC via high efficiency switch mode rectifiers rated at 3300 watts (275 amps) each and battery backup units (BBUs) rated at 3000 watts (250 amps) each. It can be configured with up to three shelves rated at 2200 amps each. The system also accommodates a System Control Card (SCC) that controls and monitors the rectifiers and BBUs while communicating to the rack management system.

BBUs, which can be installed in any rectifier slot, can be operated in two modes. In the classic backup power mode – during the loss of AC input – each BBU can deliver 3000 watts for 90 seconds. The BBUs also provide a power boost feature that delivers additional power to the system when the peak power requirement of the load temporarily exceeds the output capacity of the installed rectifies or a settable power limit value.

The modular design allows the power system's capacity to expand as your system needs grow. Each 12V DC power shelf can accept a combination of nine individual, plug-in rectifiers or battery backup units that can be easily installed live without system interruption. Each shelf provides 26400 watts (2200 A max) at 12V DC in three rack units (5.25") of height. The SCC can manage up to three shelves for a maximum system capacity of 79200 watts (6600 A max) at 12V DC.

Application

The NetSure 12V DC power system is ideal for data center racks and cabinets, either custom or standard (such as Open Compute Project).

Ordering Information

MODEL NUMBER	PART NUMBER	DESCRIPTION
PSS12/2000-19BC	588706100xx	12V DC power main shelf
PSS12/2000-19B	588706000xx*	12V DC power expansion shelf
M520H	1M520HNA	12V DC System Control Card (SCC)
R12-3300	1R123300	12V rectifier, 3300 watts
R12-3000	1R123000	12V rectifier, 3000 watts
B12-3000	1B123000	12V battery backup unit, 3000 watts

* Several options are available.



12V Rectifier (left)
Battery Backup Unit (right)



12V DC Power System Shown with
Six 12V Rectifiers, Three BBUs and One SCC

Technical Specifications

INPUT	
Voltage, Shelf	208VAC to 240VAC three-phase (3-wire + PE) with range of 176 VAC to 264 VAC 230/400VAC to 240/415VAC nominal three-phase (4-wire + PE) with range of 195/338VAC to 264/457VAC 277/480VAC nominal three-phase (4-wire + PE) with range of 235/407VAC to 310/537VAC
Voltage, Rectifier and BBU	200 VAC / 208 VAC / 220 VAC / 240 VAC / 277 VAC nominal single-phase with range of 176 VAC to 305 VAC
Current, Rectifier	20.2 amps maximum at full power and 176 VAC
Current, BBU	0.55 amps maximum at 176 VAC
Circuit Protection	Fuses located in each line input of rectifiers and BBUs
Efficiency	94% typical
OUTPUT	
Voltage	12.3 VDC nominal, adjustable from 12.0 VDC to 13.2 VDC
Current, Shelf	2200 amps maximum
Current, Rectifier	275 amps maximum at 12.0 VDC (3300 watts maximum)
Current, BBU	250 amps maximum at 12.0 VDC (3000 watts maximum) for 90 seconds
Capacity, BBU	75 Watt-Hours, 700 cycles
Regulation	Steady state output voltage remains within $\pm 1\%$ of the pre-adjusted voltage for any load current from no load to full load and over the specified input voltage range
Dynamic Response	For a step load change within the range of 10 % to 90 % of full rated current, the maximum voltage transient will not exceed 5 % of the initial steady state voltage
Filtering	Wide band noise does not exceed 120 mV peak to peak
PROTECTION	
Over-Voltage	Each rectifier and BBU will automatically shut down and lock out should its output voltage exceed a value set by the controller, maximum set point is 13.2 VDC. Unit will automatically attempt to restart once. A second (backup) over-voltage protection circuit will shut down and latch off the unit if the voltage exceeds 14.0 VDC
Over-Current	Adjustable from 25 amps to 275 amps per rectifier and from 25 amps to 250 amps per BBU
Power Limit	Non-adjustable limit of 3300 watts maximum per rectifier and 3000 watts maximum per BBU
Over-Temperature	Each rectifier and BBU will automatically shut down if the internal temperature of the module exceeds a predetermined value. Operation will automatically resume after the over-temperature condition is removed
Internal Fault On Output	Each rectifier and BBU contains an output blocking (ORing) circuit which prevents an internal fault in the unit from affecting the bus voltage
PHYSICAL CHARACTERISTICS – WEIGHT AND DIMENSIONS (H X W X D)	
Shelf	20 kg (44 lb) without AC cords, 132 mm x 483 mm x 696 mm (5.2" x 19" x 27.4")
Rectifier	3.0 kg (6.6 lb), 124 mm x 41.4 mm x 453 mm (4.9" x 1.6" x 17.8")
BBU	4.1 kg (9.1 lb), 124 mm x 41.4 mm x 453 mm (4.9" x 1.6" x 17.8")
ENVIRONMENTAL	
Operating Temperature	-10 °C to +45 °C (+14 °F to +113 °F) without BBUs, 0 °C to +45 °C (+32 °F to +113 °F) with BBUs
Storage Temperature	-40 °C to +85 °C (-40 °F to +185 °F) without BBUs, consult manual for BBU storage temperature specifications
Humidity	0 % to 95 % relative humidity, non-condensing
Altitude	-200 feet to 10000 feet, maximum operating ambient temperature should be derated linearly (3 °C per 1000 ft.) at elevation above 6000 ft
EMC	This unit conforms to the requirements of FCC Part 15, Subpart B, Class A and EN 300 386, Class A for radiated and conducted noise
Safety Compliance	UL 60950, CAN/CSA-C22.2 No. 60950-1-03, GR-3160, CE mark, RoHS, REACH

VertivCo.com | Vertiv Headquarters, 1050 Dearborn Drive, Columbus, OH, 43085, USA

© 2017 Vertiv Co. All rights reserved. Vertiv and the Vertiv logo are trademarks or registered trademarks of Vertiv Co. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness herein, Vertiv Co. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications are subject to change without notice.