

eSure™ Rectifier

R48-3000e3

Key Features

- High efficiency, reduces power consumption for lower operating costs
- Full output power (3kW) up to +45 C allows savings on climate system and operating costs
- Wide input voltage range to operate in the most demanding environments
- Hot pluggable facilitates future expansions and easy maintenance
- Compliant with global standards – delivers quality, performance and reliability no matter what the application or location demands


In addition to reducing power consumption and lowering operating cost, eSure™ high-efficiency rectifiers offer superior performance and uncompromised reliability.

Description

The 3000W high-efficiency eSure™ rectifier (model R48-3000e3) is designed to convert standard AC supply voltages into stable nominal -48 V DC voltage that is adjustable to application needs. The R48-3000e3 is a constant power rectifier designed with the latest patented switchmode technology, using DSP (Digital Signaling Processor) functionality for efficient operation.

For a higher load capacity, rectifiers can be connected in parallel, and intelligent control can be added with the help of a separate controller.





1



eSure[™] Rectifier R48-3000e3

Technical Specifications

AC Input	
Input Voltage, Nominal	200 to 250 VAC
Input Voltage, Permitted Variation	85 to 300 VAC
Line Frequency	45 to 65 Hz
Max Input Current	22 A
Power Factor	>0.99 for 50%-100% load
THD (Total Harmonic Distortion)	≤5% for 50%-100% load, ≤2%no load

DC Output	
Output Voltage, Adjustment Range	-42 to -58 V DC
Output Power	3000W Maximum
Output Power, Derated for Input Voltage	See diagram
Output Current	62.5A@-48VDC
Output Current Limit Set Point	0 to 62.5A
Peak Efficiency	95.5%
Temperature Derating	Full output power up to +45°C at input voltage range of 176-264VAC

Control and Monitoring		
Rectifier Alarm and Signaling	Alarm and status re	eported via CAN bus to system controller
Visual Indications	Green LED: Yellow LED: Red LED:	Normal Operation Alarm Failure

Environmental	
Temperature Range, Operating	-40 to 70°C,-40 to +158°F (See diagram for de-rating)
Temperature Range, Storage	-40 to +70°C, -40 to +158°F
Relative Humidity	0 to 95%
Altitude	2000 m, 6560 ft at full power
EMC	ETSI EN300 386: 2005, Class B.
	EN55022, Class B
Safety	EN 60950-1;IEC 60950


Mechanics	
Dimensions (H x W x D)	41x84.5x330mm/1.61x3.33x13 inches
Weight	1.5kg/3.41lbs


Other Parts		
Controller Units	See separate controller datasheet	


Ordering Information

Part Number	Description	
1R483000e3	High efficiency eSure™ rectifier, -48VDC,3000W	

Diagrams







VertivCo.com |