

Vertiv™ Edge Lithium-Ion UPS

1500 - 3000VA 230V

High Performance Line-Interactive Power Protection for Servers and Networking Equipment






The Vertiv[™] Edge Lithium-Ion line-interactive UPS provides a high level of power protection to your business-critical applications.

The Vertiv Edge Lithium-Ion line-interactive UPS provides both power conditioning and battery backup to critical IT equipment such as servers and network gear ensuring your business-critical applications are protected in the event of an unanticipated loss of power or an unprecedented power surge.

The Vertiv Edge Lithium-Ion UPS protects against a wide range of power fluctuations and automatically switches to battery backup when power loss is detected. With a 0.9 output power factor (PF) and less than 6 millisecond transfer time, you can ensure your most critical assets are protected.

Protects Against



High Performance Line-Interactive Power Protection

The rack-mount design of the Vertiv Edge Lithium-Ion UPS is ideal for server rooms, network closets, and other edge or distributed IT applications within small and medium businesses where floor space is at a premium. It is a true low-maintenance, set-it and forget-it solution ideal for remote locations with limited onsite technical resources.

Vertiv Edge Lithium-Ion Overview

- 1500VA, 2200VA, & 3000VA UPSs in a rack/tower convertible form factor
- Standard 5-year warranty provides peace of mind your investment is protected against potentially costly equipment failures
- Achieve the lowest total cost of ownership over the lifetime of the UPS with fewer battery replacements and up to 10 years of useable life
- Hot-swappable, user-replaceable batteries increase the useable life of the UPS by allowing you to easily replace the batteries without disrupting power to connected equipment
- Internal batteries offer industry-leading runtime (up to 10 minutes at full load) to protect critical equipment during an unexpected power loss
- Lithium-Ion battery technology degrades slower in high temperature environments, supports up to 10 times more discharge cycles, and delivers faster recharge times compared to VRLA batteries

Why should you choose Lithium-Ion Technology?

LONGER LIFE







SMALLER & LIGHTER



LONGER RUNTIME



ENVIRONMENTALLY FRIENDLY



FAST BATTERY RECHARGE







Lithium-Ion technology delivers up to 3 times the life expectancy of lead-acid batteries and lowers the total cost of ownership by nearly half

Lithium-Ion Outperforms VRLA when compared...

Battery Feature	VRLA Battery	Li-ion battery	Lithium-Ion Benefit
Standard battery life	3-5 years	8-10 years	Up to 3 times longer life
Typical cycle life	200-260	2000	Up to 10x more discharge/recharge cycles
Battery recharge time (@ 90%)	3-6 hours	<2 hours	Fast recovery time safeguards your critical IT equipment in the event of multiple outages
Battery weight	10.9 kg	5.9 kg	45% lighter making it ideal for small spaces and wall-mount racks
Warranty	2 or 3 years	5 years	Worry free operation so you can set-it and forget-it

Visit the TCO calculator at https://www.vertiv.com/en-emea/support/tools-and-application/tco-calculator/

Build Your Total Infrastructure Solution with Vertiv

Discover expert designed IT infrastructure solutions with proven success in diverse environments and countless applications.

Vertiv[™] Geist[™] rPDU

Reliable power distribution with outlet level remote monitoring and management providing the highest level of power visibility and control.

> Cable and Air Flow Management

Included accessories ensure proper cable management and airflow to keep your equipment cool.

Software and IT Management

Monitor the entire system either locally or remotely to ensure you are alerted of out-of-range conditions that could result in costly downtime.

Vertiv[™] Edge Lithium-Ion UPS

Protect mission critical equipment in the event of power loss or extreme power fluctuations.

Vertiv™ VR Rack Self-contained 42U server rack designed to simplify equipment installation and provides an additional 6cm of useable depth.

Vertiv[™] VRC

Keep critical IT equipment cool with a dedicated high-efficiency rack-mount cooling system with scalable capacity.

Visit Vertiv.com or contact a Vertiv Sales Representative today to find out how Vertiv can help you configure an all-in-one infrastructure solution.

High Performance





0.9 Output Power Factor (PF): Provides more useable power enabling you to connect more equipment saving you money and space.

Increased Runtime: Internal batteries offer up to 10 minutes of runtime at full load.

Programmable Outlet Group: Extend run time when on battery power by power-cycling connected equipment and shedding less critical loads.

Battery Backed Outlets: Up to 7 battery backed outlets ensuring critical equipment is protected.

Advanced Warning Status: Receive early audible and visual alarms warning you of system status to alert you to an input voltage fluctuation (buck/boost) output overload, low battery, or battery replacement condition.

Wide Input Voltage Range: Prolong battery life by allowing the UPS to maximize the use of the utility power before transferring to battery.

Superior Battery Technology



Fewer Battery Replacements: Lithium-Ion batteries require fewer battery replacements and last on average up to 3 times as long as traditional VRLA batteries reducing maintenance, labor, and replacement costs (lower TCO).

More Discharge Cycles: Lithium-Ion batteries deliver up to 10 times more charge / discharge cycles than VRLA batteries.

Fast Recharge: Lithium-Ion batteries recharge twice as fast as traditional VRLA batteries getting you back to 90% in as little as 2 hours.

Hot-Swappable, User-Replaceable Batteries: Increase product life and reliability with batteries that can be easily replaced without disrupting power to connected equipment.

Environmentally Friendly: Significantly reduce battery disposal and recycling with lower replacement rates.

Enhanced Manageability



LCD Display: User-friendly full-color LCD interface with gravity sensing orientation simplified installation and configuration while also providing instant at-a-glance status and insights.

Free Power Management Software:

- Vertiv[™] <u>Power Insight</u> Add the Liebert[®] IS-UNITY card for web/SNMP manageability
- Vertiv[™] Power Assist Monitor UPS conditions through a local USB connection
- Vertiv[™] Intelligence Director Together with Vertiv[™] Geist[™] rPDU one single IP Address to monitor and manage up to 50 devices

Remote Monitoring and Management: Add an optional Liebert[®] IntelliSlot IS-UNITY communication card to enable remote monitoring / management (web based, SNMP, BACnet, MODBUS and relay contacts) and environmental monitoring via external sensors.

Remote Emergency Power Off: Remotely shutdown the UPS during an emergency.



Comprehensive Services for Critical Systems

Power Emergency Package

The Power Emergency Package provides emergency support with 100% parts coverage and is available for single-phase UPS products up to 3kVA. Adding Vertiv services to your Vertiv[™] Edge Lithium-Ion UPS ensures you are protected during an emergency.

- Five years service coverage (10 with renewal)
- 24x7 professional Helpline
- Advanced replacement of the faulty unit
- Shipping costs covered by Vertiv
- Coverage for both electronic parts and battery failures
- The Power Emergency Premier version also provides remote diagnostic and preventive monitoring with Vertiv[™] LIFE[™] Services, enabled via the optional Liebert[®] Intellislot Unity Card

Installation and Start-up Services


Installation and Start-up Services provide on-site technical support for installation and start-up of your UPS or battery cabinet, ensuring you get up and running as quickly as possible:

- Installation includes mounting the new UPS and battery cabinets
- Start-up available in 2 scheduling options, in 8x5 or 24x7
- Services performed by a Vertiv factory trained technician


Service Part Number	Description	UPS applicable
	Dowor Emorgonov EVD OLD DESDOVE Crown 2	EDGELI-1500IRT2U
RUPS-PE5-003	Power Emergency 5YR-8HR RESP8X5 Group 3	EDGELI-2200IRT2U
RUPS-PE5-004	Power Emergency 5YR-8HR RESP8X5 Group 4	EDGELI-3000IRT2U
RUPS-PE5-005	Power Emergency 5YR-8HR Premier	EDGELI-3000IRT2U
PS-RUPS-INSTL247-005	Installation 1PH UPS 24X7 Group 5	EDGELI-3000IRT2U
PS-RUPS-ST85-005	Startup 1PH UPS 8X5 Group 5	EDGELI-3000IRT2U
PS-RUPS-ST247-005	Startup 1PH UPS 24X7 Group 5	EDGELI-3000IRT2U

Note: Service offerings are available only in select countries, please check with your Vertiv representative if yours is included. Timing may vary depending on local country public holidays and other considerations. Please refer to the appropriate Scope of Work for additional details.






EDGELI-3000IRT2U



EDGELI-2200IRT2U



- Input circuit breaker
- 2 AC Input
- 3 USB communication port
- IntelliSlot port (optional communications card)
- Programmable output receptacles (1 group)
- 6 Non-programmable output receptacles
- Emergency Power Off (EPO) connector
- Output circuit breakers
- 9 Earth terminal

What's In The Box

- Vertiv[™] Edge Lithium-Ion UPS
- USB type A to B cable
- 4-post rail kit
- Screws, ears and mounting hardware
- Tower feet
- 2 x IEC C13 to C14 output cables
- Input power cables (UK, AUS, Schuko)
- Vertiv[™] Power Assist and Vertiv[™] Power Insight management software (free download)
- Quick Installation Guide
- Safety Instructions

Technical Specifications

	EDGELI-1500IRT2U	EDGELI-2200IRT2U	EDGELI-3000IRT2U 3000VA / 2700W Rack / Tower (2U)		
Power Rating (VA/W)	1500VA / 1350W	2200VA / 1980W			
Form Factor	Rack / Tower (2U)	Rack / Tower (2U)			
Dimensions, mm					
nit (W x D x H) 438 x 410 x 86		438 x 510 x 86	438 x 630 x 86		
hipping (W x D x H)	550 x 620 x 240	565 x 700 x 240	600 x 800 x 240		
Veight, kg					
nit	12.8	17.5	24.3		
hipping	20.4	25.2	32.1		
nput AC Parameters					
oltage Range Without Battery Operation 230V default)	166 - 278V	166 - 278V	166 - 278V		
requency Range	45 - 65Hz, autosensing	45 - 65Hz, autosensing	45 - 65Hz, autosensing		
nput Power Connector	IEC60320 C14	IEC60320 C20	IEC60320 C20		
urge Protection	624J	624J	624J		
output AC Parameters					
utput Receptacles	3 + 3 IEC60320 C13	3 + 3 IEC60320 C13 + 1 IEC60320 C19	3 + 3 IEC60320 C13 + 1 IEC60320 C19		
utput Receptacles - Controllable	Yes - 1 group (3 x IEC60320 C13)	Yes - 1 group (3 x IEC60320 C13)	Yes - 1 group (3 x IEC60320 C13)		
utput Voltage	200/208/220/230 (default) /240	200/208/220/230 (default) /240	200/208/220/230 (default) /240		
aveform (Battery Operation)	Pure Sine Wave	Pure Sine Wave	Pure Sine Wave		
ransfer Time	4 - 6 ms Typical	4 - 6 ms Typical	4 - 6 ms Typical		
utput Overload (AC Mode)	111% - 120% @ 10 s > 121% - Shutdown	111% - 120% @ 10 s > 121% - Shutdown	111% - 120% @ 10 s > 121% - Shutdown		
fficiency (full load, interactive mode)	97.5%	98.5%	98.5%		
attery					
уре	Li-ion (LiFePo4)	Li-ion (LiFePo4)	Li-ion (LiFePo4)		
uantity & Voltage & Capacity	1 x 48V x 5Ahr	2 x 72V x 2.5Ahr	3 x 72V x 2.5Ahr		
echarge Time 30% / 100%, from full discharge)	1.7 hrs / 1.9 hrs	1.7 hrs / 1.9 hrs	2.4 hrs / 2.7 hrs		
ull-Load Runtime	8.7min	9.3min	10.5min		
alf-Load Runtime	18.5min	20.2min	22.6min		
nvironmental					
perating Temperature	0 to 40°C	0 to 40°C	0 to 40°C		
torage Temperature	-10°C to +45°C	-10°C to +45°C	-10°C to +45°C		
elative Humidity (Operation)	8% to 90%, non-condensing	8% to 90%, non-condensing	8% to 90%, non-condensing		
perating Altitude (without derating)	3000m	3000m	3000m		
udible Noise (line mode)	<45dBA AVR mode, >70% load < 55dBA Battery mode	<45dBA AVR mode, >70% load < 55dBA Battery mode	<45dBA AVR mode, >70% load < 55dBA Battery mode		
Igency					
ompliance*	CE, CB Report, EAC, RCM, UKCA	CE, CB Report, EAC, RCM, UKCA	CE, CB Report, EAC, RCM, UKCA		
afety	EN62040-1:2008+A1:2013 CB - IEC62619 li-ion battery	EN62040-1:2008+A1:2013 CB - IEC62619 li-ion battery	EN62040-1:2008+A1:2013 CB - IEC62619 li-ion battery		
nvironmental	RoHS2 / REACH / WEEE	RoHS2 / REACH / WEEE	RoHS2 / REACH / WEEE		
nsportation ISTA 2A UPS UN38.3 (Lithium-Ion)		ISTA 2A UPS UN38.3 (Lithium-Ion)	ISTA 2A UPS UN38.3 (Lithium-Ion)		
ommunications and Management					
lot for optional cards	Yes	Yes	Yes		
ommunication port	USB	USB	USB		
mergency Power Off (EPO)	Yes	Yes	Yes		
Varranty					
Varranty	5 years on UPS and Battery	5 years on UPS and Battery	5 years on UPS and Battery		

*For a full list of compliance certificates please contact your local Vertiv representative.



Vertiv[™] Edge Lithium-Ion UPS Runtimes

Vertiv [™] Edge Lithium-Ion 1500VA EDGELI-1500IRT2U		Ver	Vertiv [™] Edge Lithium-Ion 2200VA EDGELI-2200IRT2U			Vertiv [™] Edge Lithium-Ion 3000VA EDGELI-3000IRT2U					
Load%	VA	Watts	Runtime (min)	Load%	VA	Watts	Runtime (min)	Load%	VA	Watts	Runtime (min)
100%	1500	1350	8.7	100%	2200	1980	9.3	100%	3000	2700	10.5
90%	1350	1215	9.7	90%	1980	1782	10.5	90%	2700	2430	11.8
80%	1200	1080	11.1	80%	1760	1584	12.0	80%	2400	2160	13.5
70%	1050	945	12.9	70%	1540	1386	13.9	70%	2100	1890	15.6
60%	900	810	15.3	60%	1320	1188	16.6	60%	1800	1620	18.6
50%	750	675	18.5	50%	1100	990	20.2	50%	1500	1350	22.6
40%	600	540	23.5	40%	880	792	25.5	40%	1200	1080	28.6
30%	450	405	31.4	30%	660	594	34.3	30%	900	810	38.5
20%	300	270	43.7	20%	440	396	47.1	20%	600	540	52.4
10%	150	135	84.9	10%	220	198	90.7	10%	300	270	102.6


Vertiv[™] Edge Lithium-Ion Accessories

MicroPOD – Maintenance Bypass and Output Distribution

UPS Model Number	MicroPOD Model Number	Input Connection	Output Connection
EDGELI-1500IRT2U	MP2-210K	IEC60320-C14	4+4 IEC60320-C13
EDGELI-2200IRT2U	MP2-220L	IEC60320-C20	2+2+2 IEC60320-C13 & 1 IEC60320-C19
EDGELI-3000IRT2U	MP2-220L	IEC60320-C20	2+2+2 IEC60320-C13 & 1 IEC60320-C19



Model Number	Applicable To	Description
PSI5-1500LIBATKIT	EDGELI-1500IRT2U	48V x 5Ahr (LiFe-485000 x 1)
PSI5-2200LIBATKIT	EDGELI-2200IRT2U	72V x 2.5Ahr (LiFe-722500 x 2 parallel)
PSI5-3000LIBATKIT	EDGELI-3000IRT2U	72V x 2.5Ahr (LiFe-722500 x 3 parallel)



Model Number	Description
IS-UNITY-SNMP	10/100 Mbit Ethernet SNMP, Device Web Page, with MIB and configuration cable
IS-UNITY-DP	Same as IS-UNITY-SNMP, plus SN Series environmental sensor support
IS-RELAY	Intellislot Interface Kit for Relay Contacts

Environmental sensors (for Unity cards)

Model Number	Description
SN-T	Modular with single temperature sensor
SN-TH	Modular with single temperature and humidity sensor
SN-2D	Modular with two door contact inputs
SN-3C	Modular with three dry-contact inputs
SN-Z01	Integrated cable with single temperature sensor
SN-Z02	Integrated cable with three temperature sensors
SN-Z03	Integrated cable with three temperature sensors & one humidity sensor











Vertiv.com | Vertiv Infrastructure Limited, George Curl Way, Southampton, SO18 2RY, VAT Number: GB188146827

© 2021 Vertiv Group Corp. All rights reserved. Vertiv" and the Vertiv logo are trademarks or registered trademarks of Vertiv Group Corp. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness here, Vertiv Group Corp. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications, rebates and other promotional offers are subject to change at Vertiv's sole discretion upon notice.