


$Vertiv^{{}^{\scriptscriptstyle{\mathrm{TM}}}}\,SmartMod^{{}^{\scriptscriptstyle{\mathrm{TM}}}}$

Modular Data Center Infrastructure



Vertiv[™] SmartMod[™]

Imagine the advantages of a rapidly deployable, standalone data center with all the capabilities you need to achieve your IT objectives.



Building a new data center in a short timeframe is nearly impossible. The Vertiv[™] SmartMod[™] provides enhanced levels of availability, efficiency, and control in selfcontained enclosures that can be deployed securely, virtually anywhere. For IT deployments between 2 and 14 racks with 100 kW or less, SmartMod offers a simple way to install capacity in a fraction of the time.

You don't have to overspend, or overbuild based on uncertain future needs – with right-sized systems designed to work together and optimized for constructability; you can build just what you need today, better aligning your capital plans to your business challenges.

SmartMod leverages core Vertiv Critical Power, Thermal Management, and Monitoring & Control technologies.

SmartMod incorporates:

- Modular and scalable Vertiv[™] Liebert[®] UPS power protection
- Close-coupled in-row Liebert[®] CRD thermal management units with intelligent iCOM[™] Edge controls

- Classic and cost-effective Vertiv racks
- Vertiv rack PDUs
- Thermal containment to isolate hot aisle and cold aisle airflows for optimum thermal performance
- Automatic Transfer Switch (ATS) to reliably select normal or emergency power sources
- Overhead infrastructure, including piping, electrical distribution, and fiber ducts
- Clean agent fire suppression and aspiration smoke detection (as optional items)
- Vertiv[™] Critical Insight real-time monitoring and visualization for critical infrastructure (as optional item)

All subsystems are factory installed into a secure, weatherproof and transportable enclosure – simplifying and drastically shortening the on-site time required to install and startup, and reducing the potential for risk, quality, or schedule delays.

Cutaway illustration of Vertiv™ SmartMod™

SmartMod is not a one size fits all system. It is designed to be configurable to right-size to your rack footprint, IT load, desired redundancy, location, and other additional options so you can achieve the optimal solution based on a specific need.


When deploying multiple units or at numerous locations, having a standard look and feel, layout and equipment kit simplify maintenance and operations activities. Vertiv backs it all up with the service and support network you have come to expect from us.



Cutaway illustration of Vertiv[™] SmartMod[™]



Component Overview of Vertiv[™] SmartMod[™]



Cutaway view of Vertiv™ SmartMod™



Top view of Vertiv™ SmartMod™

4





SmartMod[™] Specifications

Standard Design Specifications	SmartMod™
Enclosure External Dimensions	
Enclosure Length (mm)	6426, 8010, 9594, 11178 or 11970
Enclosure Width (mm)	3400
Enclosure Height (mm)	3260
Module Overall Length [1]	6426-12045 mm (@ 6426 mm) 8010-13630 mm (@ 8010 mm) 9594-15215 mm (@ 9594 mm) 11178-16795 mm (@ 11178 mm) 11970-17590 mm (@ 11970 mm)
Lifting Weight ^[2]	Up to 18000 kg per module
Input AC Parameters	
Region	EMEA
Voltage/Frequency	400 VAC, 50 Hz
IT Racks	
Rack Height	42U (2000 mm) 47U (2200 mm) 48U (2265 mm)
Rack Depth	1100 mm
Rack Width	600 mm and/or 800 mm
Rack Load	8 kN
Electrical	
Electrical Distribution Board	1 or 2
Automatic Transfer Switch	1 or 2
UPS Model	APM150
UPS Cabinet	1 or 2
UPS Module Redundancy	N or N+1
UPS Rating	Up to 150 kVA (@ APM150)
Battery Backup Time ^[3]	Up to 13 min @ 100 kW Up to 30 min @ 50 kW
Busbar System	2 per row
Rack Load	Up to 17 kW
PDU	2 per rack
PDU Capacity (max)	3x32 A @ 230/400 V-3 phase
PDU Type	Basic, Monitored (unit level) or Switched (unit level)
Mechanical (HVAC)	
Air Conditioning Type	In-row, direct expansion
Air Conditioning Redundancy	N or N+1
Air Conditioning Units	up to 6x CRD25 with up to 6x CCD25 externally mounted condensers
Cooling Capacity for IT Load (35°C)	up to 100 kW
Exterior Ambient Operating Range	-30°C to +52°C

Length presented is the maximum transport length. It includes an enclosure with attached condenser units.
Weight presented is the estimated weight of shipping/lifting the unit with empty IT racks and empty UPS battery cabinets.
Battery backup time at beginning of life (BOL). Maximum available backup time may vary based on solution input parameters (presented here 2 options for different IT Load requirements).



Vertiv.com | Vertiv Croatia d.o.o.

© 2022 Vertiv Group Corp. All rights reserved. Vertiv[™] and the Vertiv logo are trademarks or registered trademarks of Vertiv Group Corp. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness here, Vertiv Group Corp. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications, rebates and other promotional offers are subject to change at Vertiv's sole discretion upon notice.