



**BUREAU
VERITAS**

Zertifikat Certificate

Zertifikatsinhaber:
Holder of certificate:

Knürr GmbH
Mariakirchener Str. 38
94424 Arnstorf
Germany

Handelszeichen:
Trademark:
(if other than applicant)
Fertigungsstätte:
Factory:

KNÜRR

Produkt-Typ:
Product type:

IT Power Distribution Unit (PDU) / Multiple Socket Outlet

Modell:
Model:

DI-STRIP PDU 50A
DI-STRIP BladePower (single- and three-phase models)
DI-STRIP PizzaPower

Single-phase models

DI-STRIP PizzaPower 1~
DI-STRIP PizzaPower M 1~
DI-STRIP PizzaPower RM 1~

3-phase models

DI-STRIP PizzaPower 3~
DI-STRIP PizzaPower M 3~
DI-STRIP PizzaPower RM 3~

Nenndaten:
Ratings:
Zulassungszeichen:
Certification mark:

siehe Anhang
see Annex




Repräsentative Testmuster des/der o. g. Modells/Modelle bestanden die Prüfungen nach
Representative test samples of above stated model(s) passed the tests according to

Norm:
Standard:
Bericht Nr.:
Report no.:
Zertifikat Nr.:
Certificate no.:
Datum:
Issued:

IEC 60950-1:2005 (Second Edition) + Am 1:2009 + Am 2:2013 and
EN 60950-1:2006 +A11:2009 +A1:2010 +A12:2011 +AC:2011 +A2:2013
07KFS113-60950_6, 05KFS173-60950_5, 06KFS076-60950_4

013-02-EEBG P17

2017-01-17 **Gültig bis:** 2022-01-16
Valid until:



Heinz-Jürgen Zeiger



**BUREAU
VERITAS**

Anhang zu Zertifikat 013-02-EEBG P17 Annex to certificate

Nenndaten:
Ratings:

DI-STRIP PDU 50A			
Input:	100 – 240 Vac; 50 – 60 Hz; max. 50 A		
Output:	100 – 240 Vac	Outlets:	Sheet F max. 10 A
			Sheet J max. 16 A

DI-STRIP BladePower (single- and three-phase models)			
Input:	1~ 100 – 240 Vac; max. 32 A; 50 – 60 Hz 3~ 100 – 240/173 – 415 Vac; max. 32 A; 50 – 60 Hz		
Output:	1~ 100 – 240 Vac	Outlets:	Sheet F max. 10 A
			Sheet J max. 16 A

Model description

Mains connection:

Power supply cord options:

- IEC 60309 plug (2P + PE or 4P + PE)
- glossy cut
- crimped ferrules
- ring terminals

Socket-outlet options:

- a) national
 - DE (CEE7) 16 A
 - FR (CEE7) 16 A
 - CH (SEV 1011) 10 A
- b) international
 - Sheet F 10 A
 - Sheet J 16 A

Other options:

- line monitor (LED Display)
- AC amperemeter (one per phase or outlet-combination)
- thermal circuit breaker with reset (one per x-outlet)



**BUREAU
VERITAS**

Anhang zu Zertifikat 013-02-EEBG P17 Annex to certificate

Nenndaten:
Ratings:

DI-STRIP PizzaPower			
Input:	1~ 100 - 240 Vac; max. 32 A; 50 – 60 Hz 3~ 100 - 240/173 - 415 Vac; max. 32 A; 50 – 60 Hz		
Output:	100 – 240 Vac	Outlets:	Sheet F max. 10 A
			Sheet J max. 16 A
			CEE max. 32 A

Model description

The following models (DI-STRIP Pizza Power ...) existed when the test report was issued.

...	P/N	AMM	RMM	Plug	total no. of outlets	no. of C13 outlets	no. of C19 outlets	no. of CEE outlets	feature	housing length (mm)
1~	03.631.807.1				7	7				400
1~	03.631.007.1			X	7	7				400
1~	03.631.124.1			X	16	12	4			720
1~	03.631.240.1			X	24	24	0			960
1~	03.631.214.1			X	25	21	9			1017
M1~	03.636.007.1	X		X	7	7				483
RM1~	N/A		X							
RM1~	03.637.023.1		X	X	24	24				1110,5
RM1~	03.637.016.1		X	X	16	12	4			870,5
RM1~	03.637.025.1		X	X	25	21	4			1167,5
3~	03.631.821.1				21	21				933
3~	03.631.021.1			X	21	21				933
3~	03.631.006.1			X	6		6			408
3~	03.631.912.1			X	21	9	12			939
3~	03.631.360.1			X	36	36				1362
3~	03.631.186.1			X	24	18	6			1002
M3~	03.636.021.1	X		X	21	21				933
RM3~	03.636.021.1-000001		X		24	18	6		+ LS-switch	1276,5
RM3~	03.637.006.1		X	X	6		6			562,5
RM3~	03.637.018.1		X	X	18	6	12			994,5
RM3~	03.637.021.1		X	X	21	21				1021,5
RM3~	03.637.024.1		X	X	24	18	6			1156,5
RM3~	03.637.042.1		X	X	42	36	6			1750,5
RM3~	03.637.006.1-000002		X		6			6		843,7

NOTE: Additional equivalent models with different part numbers may exist in the future.