



Disclosure and photocopying of this document, exploitation and communication of its contents are not permitted, unless permission is expressly granted. All rights are reserved.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwendung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Alle Rechte vorbehalten.



AGENCY COMPLIANCE:  
 - UL certification: UL 60950-1 (2nd), CSA C22.2 No. 60950-1-07  
 - FCC certification  
 - CB certification: IEC 60950-1 (2nd)  
 - "-100" SUFFIX (PSE MODELS): INTERPRETATION OF DENAN TECHNICAL REQUIREMENTS MINISTERIAL ORDINANCE APPENDIX 12, J60950-1(H26), J55022(H22)

ENVIRONMENTAL RATING:  
 OPERATING TEMPERATURE: 5 °C - 60 °C (41 °F - 140 °F) NON-CONDENSING, NON-CORROSIVE, 10 % - 90 % RH  
 STORAGE TEMPERATURE: -20 °C - 85 °C (-4 °F - 185 °F)  
 MAX. OPERATING ALTITUDE: 2000 m

NOTES:  
 1. UNIT DIMENSIONS: 1736.5 mm (68.4") H x 50 mm (2.0") D x 56 mm (2.2") W  
 2. UNIT WEIGHT: 4 kg / 8.8 lbs  
 3. SHIPPING DIMENSIONS: 2017.0 mm (79.4") H x 297 mm (11.7") D x 176 mm (7.0") W  
 4. SHIPPING WEIGHT: 6.8 kg / 15 lbs  
 5. (2) MOUNTING BUTTONS AND (2) MOUNTING BRACKETS SUPPLIED WITH EACH UNIT. EITHER OPTION CAN BE USED TO MOUNT THE PDU.

| BRANCH | PHASE | RECEPTACLE TYPE (QUANTITY) | VOLTAGE (V) | MAX. CONTINUOUS AMPS (A) |            |
|--------|-------|----------------------------|-------------|--------------------------|------------|
|        |       |                            |             | PER RECEPTACLE           | PER BRANCH |
| A      | L1-L2 | 9xC13, 3xC19               | 200-240     | 12/16                    | 16         |
| B      | L1-L2 | 9xC13, 3xC19               | 200-240     | 12/16                    | 16         |

| INPUT CORD  | INPUT PLUG  | WIRE COUNT | FREQUENCY (Hz) | VOLTAGE (V) | RATED AMPS (A) | MAX. CONT. AMPS (A) |
|-------------|-------------|------------|----------------|-------------|----------------|---------------------|
| 10 ft / 3 m | NEMA L6-30P | 2/PE       | 50/60          | 200-240     | 30             | 24                  |

| METERING PARAMETER | MEASUREMENT ACCURACY   |
|--------------------|--|
| VOLTAGE            | ±1 % + 0.1 VAC   |
| CURRENT            | ±1.5 % + 0.01 A FROM 1 % TO 10 % OF UNIT RATING; ±1 % FROM >10 % TO 125 % OF UNIT RATING |

RoHS COMPLIANT

|                      |   |            |                      |  |                       |
|----------------------|---|------------|----------------------|--|-----------------------|
| <br>Dimensions in mm | Allgemeintoleranzen<br>General tolerances |            | Oberfläche<br>Finish | Werkstoff / Material                       | Gewicht:<br>Weight: - |
|                      | -   |            | -                    | -  | -                     |
|                      | Drawn                                     | 15/01/16   | Name                 | Bezeichnung / Description                  |                       |
|                      | Checked                                   | 15/01/16   | Blass                | MPH2-NCV_L6-30P_18N-60                     |                       |
|                      | Approved                                  | -          | Votýpka              | Input and Branch Metered + Outlet Switched |                       |
|                      | <br>VERTIV™                               |            |                      | Zeichnungs-Nr. / Drawing no.               | Maßstab<br>Scale      |
|                      |   |            |                      | MPHC1112                                   |                       |
| Rev.                 | Change                                    | Date       | Name                 | Verwendet in / Used in                     | Blatt/Sheet           |
| B                    | 18131                                     | 01.06.2017 | Petrů                | -  | 1/1                   |