

OVERVIEW

Upgradeable Unit Level EC Monitored rPDUs provide reliable power distribution to critical IT equipment while delivering a comprehensive view of input level power usage via remote network access. Includes environmental monitoring capabilities to obtain real-time environmental metrics. Upgrade the hot-swappable monitoring device on select units to leverage new technologies and accommodate changing business needs.

Benefits

- Reliable power distribution with local and remote power monitoring options offer quick access to critical power usage information to evaluate energy usage trends and maximize uptime.
- Environmental monitoring capabilities with the addition of optional environmental sensors ensure users have critical infrastructure data at their fingertips to prevent climate-related equipment failure and system downtime.
- Gather comprehensive power data at the palm of your hand with the use of the Vertiv VLC mobile app.
- Fault-Tolerant Daisy Chaining with RSTP simplifies intelligent rPDU connectivity and ensures data is reported even when a break in the network chain occurs. Supports up to 40 rPDUs.
- Every unit is 100% tested for reliability and functionality.



Part #: VP8865

Model Number: MN03E4W1-44MB19-3TL21A0B10-S

Category: Monitored

Sub Category: Unit Level EC

Power Configuration: 30A, 120/208V WYE, 8.6kW

Physical Configuration: 72in / 1829mm, Vertical

Product Summary:

VP8865 - rPDU, Monitored Unit Level EC, 30A, 120/208V WYE, 8.6kW, Vertical, (36) IEC C13, (6) IEC C19, (2) NEMA 5-20R, 10ft power cord with L21-30P, Black Powder Coat.

Monitoring:

Input and per Phase power monitoring with Circuit/Breaker current monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility LED display.

Plug Form:



L21-30P

Receptacle:



IEC C13
(Quantity: 36)



IEC C19
(Quantity: 6)



NEMA 5-20R
(Quantity: 2)

Chassis Color Options:



To discuss color options, contact your local sales representative.

Product Specification and Options

System Features

Monitoring	Input and per Phase power monitoring with Circuit/Breaker current monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility LED display.
Monitoring Level 1	Aggregate - Total Unit Monitoring (kWh, W, VA, PF) Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements
Monitoring Level 2	Phase (A, B, C) Monitoring (kWh, W, VA, PF, V, A) Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements
Monitoring Level 3	Circuit / Breaker Monitoring (A) Circuit/Breaker Current Measurements Independently Tested and Verified at 2% Accuracy
VLC Support	Yes
Quantity Of Inputs	1
Voltage	100-120/200-240V WYE
Current	30A x 3 Phase WYE
VA per Input (Load Capacity)	8.6kW (208V)
Over Current Protection	(3) 20A Double Pole Magnetic Breakers
Switch	Breaker/Switch Combination
Scrolling / Rotatable Digital Display	Yes
Power Cable Wire Gauge	10/5
Power Cable Length	10ft
Power Entry Location	Bottom End
Plug Type	NEMA L21-30P Twistlock
Combined Total Receptacle/Socket Quantity	44
Receptacle/Socket Type #1	IEC C13
- Quantity on Face	36
- Quantity per Breaker and Phase Combination	12
- Voltage per Receptacle/Socket	208V
Receptacle/Socket Type #2	IEC C19
- Quantity on Face	6
- Quantity per Breaker and Phase Combination	2
- Style	Individual
- Voltage per Receptacle/Socket	208V
Receptacle/Socket Type #3	NEMA 5-20R
- Quantity on Face	2
- Quantity A Phase Only	2
- Style	Duplex
- Voltage per Receptacle/Socket	120V
Internal RMS Voltage Sensor	Yes
Internal RMS Current Sensor	Yes
Network Connection	Dual 10/100Mbps Ethernet

Network Protocols Supported and Data Access Formats	HTTP, HTTPS (TLS 1.2), SMTP, SMTPS (TLS 1.2), ICMP, DHCP, IPv4, IPv6, Syslog, SNMP v1/v2c/v3, JSON, JSON API, RSTP
Data Access Formats	CSV datalog, JSON API, JSON datalog
USB Support	Yes
IP Reset Button	Yes
Hard Reboot Button	Yes
Serial Connection	RS232 via RJ45
Remote Sensor RJ Connection Jacks	1 (Supports up to 16 Sensors)
Continuous Operating Temperature Range	Full nameplate operation: 10-45C / 50-113F
Continuous Operating Temperature Range	50% derated operation: 45-60C / 113-140F (See product manual or quick-start guide for full de-rated operating conditions)
Heavy Steel - Powder Coat Finish	Black
7938 Vertical Mounting Bracket Kit	Yes
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
Made in the USA	Yes, TAA Compliant
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	FCC Part 15 Class A Conformance
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	72in x 2in x 2in
Shipped Weight	17lbs (7.71kg)