



Disclosure and photocopying of this document, exploitation and communication of its contents are not permitted, unless permission is expressly granted. All rights are reserved.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Alle Rechte vorbehalten.




 NEMA L21-30P
 (30 A, 3/N/PE,
 100-120/200-240 V)

AGENCY COMPLIANCE:
 UL & c-UL Listed 60950
 RoHS Compliant
 FCC Part 15 Class A Conformance

ENVIRONMENTAL RATING:
 Maximum Operating Temperature: 60C / 140F

NOTES
 UNIT DIMENSIONS: 72in x 2.0in x 2.0in / 1829mm x 51mm x 51mm
 SHIPPED WEIGHT: 17lbs (7.71kg)
 SHIPPING DIMENSIONS: 86in x 9in x 7in / 2172mm x 223mm x 159mm
 Toolless Mounting Hardware 61.25in / 1556mm and 64.75in / 1645mm


OUTPUT POWER

CIRCUIT	PHASE	RECEPTACLE TYPE (QUANTITY)	VOLTAGE (V)	MAX. CONTINUOUS AMPS (A)	
				PER RECEPTACLE	PER CIRCUIT
1	A-B	12xC13, 2xC19, 2x5-20R A only	200-240 (IEC), 100-120 (NEMA)	12/16 (IEC), 12 (NEMA)	16
2	B-C	12xC13, 2xC19	200-240	12/16	16
3	C-A	12xC13, 2xC19	200-240	12/16	16

INPUT POWER

INPUT CORD	INPUT PLUG	WIRE COUNT	FREQUENCY (Hz)	VOLTAGE (V)	RATED AMPS (A)	MAX. CONT. AMPS (A)
10 FT	NEMA L21-30P	3/N/PE	50/60 Hz	100-120V/200-240V	30	24

METERING PARAMETER	MEASUREMENT ACCURACY
VOLTAGE	±1%
CURRENT	±1% - Input Current ±2% - Circuit/Breaker Current

 Dimensions in mm	Allgemeintoleranzen General tolerances		Oberfläche Finish		Werkstoff / Material		Gewicht: Weight: -
	-		-		-		
		Date	Name		Bezeichnung / Description		
		Drawn	10/05/18	SW		Monitored, Vertical, 30A, 120/208V WYE, (36)C13/(6)C19/(2)5-20R	
		Checked	-	-			
		Approved	-	-			
				Zeichnungs-Nr. / Drawing no.		Maßstab Scale	
				VP8865		1:6	
				Verwendet in / Used in		Blatt/Sheet	
				-		1/1	
Rev.	Change	Date	Name		