LIEBERT® GXT MT + 1 kVA - 3 kVA Gen. 2





Liebert® GXT MT+ Gen. 2 features true on-line double conversion technology, delivering best-in-class power protection for critical applications

The new Liebert GXT MT+ Gen. 2 has been designed according to comprehensive technical specifications, allowing it to provide a high level of availability for connected IT equipment.

Its Eco mode function is in charge of delivering high levels of efficiency, leading to optimized total cost of ownership (TCO) advantages.

Liebert GXT MT+ furthermore offers intelligent monitoring and network management functions for improved system shutdown and control.

This high performance UPS with proven reliability is available in a compact tower design.

Flexibility:

- Multiple communication options (USB, RS232)
- Network and volt-free contact cards (optional)
- Schuko and IEC output sockets
- Frequency converter operation 50/60 Hz.

Higher Availability:

- Wide input voltage range
- Input circuit breaker
- Automatic frequency detection.

Optimized Total Cost of Ownership:

- Eco mode for high efficiency
- Minimized installation time and costs.

Ideally Suited for:

- VoIP equipment
- Small office networks
- Computer rooms
- Process automation equipment
- Network storage devices.





Liebert GXT MT+ 1 kVA - 3 kVA Gen. 2



Liebert® GXT MT + 1 kVA - 3 kVA Gen. 2 Specifications

MODEL NUMBER	GXT MT+ 1 KVA G2 ES	GXT MT+ 2 KVA G2 ES	GXT MT+ 3 KVA G2 ES	
Power Rating	1000 VA / 800 W	2000 VA / 1600 W	3000 VA / 2400 W	
DIMENSIONS, W x D x H - mm				
Unit	145 x 282 x 223	145 x 397 x 238	190 x 421 x 336	
Shipping	230 x 360 x 325	230 x 472 x 325	320 x 560 x 460	
WEIGHT - KG				
Unit	9.7	17.3	27.5	
Shipping	10.7	18.7	29.5	
INPUT AC PARAMETERS				
Voltage Range Without Battery Operation ⁽¹⁾		From 110 to 300 V AC		
Frequency Range (synchronization)		47 - 53 or 57 - 63 Hz; Autosensing		
Input Socket	1 x IEC	1 x IEC 320 - C14		
Output Sockets		3 x IEC320 C13 & 1 x Schuko		
Voltage		220 / 230 / 240 V AC		
Waveform		Sinewave		
BATTERY PARAMETERS				
Туре		Valve-regulated, non-spillable, lead acid		
Internal Batteries		Yes		
Quantity x Voltage x Rating	2 x 12 V x 9 Ahr	4 x 12 V x 9 Ahr	6 x 12 V x 9 Ahr	
Recharge Time		4 hours recovers to 90% capacity (Typical)		
External Battery Cabinets		Not permitted		
ENVIRONMENTAL				
Operating Temperature		0 °C to 40 °C		
Relative Humidity		20% to 90% non condensing		
Operating Altitude		<1000 m without derating		
Audible Noise		<50 dBA @1 meter		
STANDARDS AND CERTIFICATIONS				
Safety		EN62040-1:2008		
EMC		EN62040-2:2006 class C2		
Compliance		CE		

 $^{^{(1)}}$ From 110 V to 175 V AC, and 280 V to 300 V AC, derating applies. Note: External battery cabinets are not permitted. Internal batteries only.



Liebert GXT MT+ G2 - 1 kVA

Liebert GXT MT+ G2 - 2 kVA

Liebert GXT MT+ G2 - 3 kVA

Tech Support

Always On! Our Commitment to your daily Business, provided by multi language Tech Support.

Toll-free 0080011554499 Toll +39 02 98250222 eoc@VertivCo.com

VertivCo.com | Emerson Network Power Limited, George Curl Way, Southampton, SO18 2RY, VAT Number: GB188146827

© 2016 Vertiv Co. All rights reserved. Vertiv[™], the Vertiv logo and Liebert* GXT MT + 1 kVA - 3 kVA Gen. 2 are trademarks or registered trademarks of Vertiv Co. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness herein, Vertiv Co. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications are subject to change without notice.