

OVERVIEW

Basic rPDUs deliver reliable power to critical IT equipment within a rack or cabinet.

Benefits

- Reliable rack power distribution.
- Every unit is 100% tested for reliability and functionality.
- Simple and convenient configuration options for cord lengths and chassis colors.

Part #: F0127977

Category: Basic**Sub Category:** Standard**Power Configuration:** 32A, 230V, 7.3kW**Physical Configuration:** 1683mm x 51mm x 51mm, Vertical**Product Summary:**

Basic Standard, 32A, 230V, 7.3kW, Vertical, (20) IEC C13, (6) IEC C19, Breakered, 3m power cord 2P+E (IP44), Black Powder Coat

Plug Form:

2P + E
(IP44)

Receptacle:

IEC C13
(Quantity: 20)



IEC C19
(Quantity: 6)

Chassis Color Options:

Part #: F0127977**Product Specification and Options****System Features**

Quantity Of Inputs	1
Voltage	220-240V
Current	32A
VA per Input (Load Capacity)	7.3kW (230V)
Frequency	50/60Hz
Over Current Protection	(2) 16A Single Pole Magnetic Breakers
Switch	Breaker/Switch Combination
Power Cable Length	3m
Power Cable Wire Gauge	4mm ²
Plug Type	IEC60309 2P + E, 32A, 250V, Splash proof IP44
Receptacle/Socket Type #1	IEC C13
- Quantity	20
- Quantity per Breaker	10
- Maximum Output per Receptacle/Socket	10A
- Voltage per Receptacle/Socket	230V
Receptacle/Socket Type #2	IEC C19
- Quantity	6
- Quantity per Breaker	3
- Maximum Output per Receptacle/Socket	16A
- Voltage per Receptacle/Socket	230V
Maximum Operating Temperature	45°C/113F
Heavy Steel - Powder Coat Finish	Black
Configuration	OU, Vertical
Toolless mounting HW – Center to Center	1560mm and 1645mm (vertical mounting bracket included)
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	CE, EN55032 & EN55024, IEC62368-1, RoHS
Chassis Dimensions (HxWxD)	1683mm x 51mm x 51mm