


Disclosure and photocopying of this document, exploitation and communication of its contents are not permitted, unless permission is expressly granted. All rights are reserved.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwendung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Alle Rechte vorbehalten.



AGENCY COMPLIANCE:
 - UL certification: UL 60950-1 (2nd), CSA C22.2 No. 60950-1-07
 - CE-mark: LVD, EMC, RoHS (incl. harmonized standards hereunder)
 - CB certification: IEC 60950-1 (2nd)
 - BG certification: BV-BG (factory inspected)
 - WEEE COMPLAINT

ENVIRONMENTAL RATING:
 OPERATING TEMPERATURE: 5 °C - 60 °C (41 °F - 140 °F) NON-CONDENSING, NON-CORROSIVE, 10 % - 90 % RH
 STORAGE TEMPERATURE: -20 °C - 85 °C (-4 °F - 185 °F)
 MAX. OPERATING ALTITUDE: 2000 m

NOTES:
 1. UNIT DIMENSIONS: 1736.5 mm (68.4") H x 50 mm (2.0") D x 56 mm (2.2") W
 2. UNIT WEIGHT: 4 kg/8.8 lbs
 3. SHIPPING DIMENSIONS: 2017 mm (79.4") H x 297 mm (11.7") D x 176 mm (7.0") W
 4. SHIPPING WEIGHT: 6.81 kg/15 lbs
 5. (2) MOUNTING BUTTONS AND (2) MOUNTING BRACKETS SUPPLIED WITH EACH UNIT. EITHER OPTION CAN BE USED TO MOUNT THE PDU.

OUTPUT POWER



BRANCH	PHASE	RECEPTACLE TYPE (QUANTITY)	VOLTAGE (V)	MAX. CONTINUOUS AMPS (A)	
				PER RECEPTACLE	PER BRANCH
A	L1	30xC13, 6xC19	100-240	10/16	16

INPUT POWER

INPUT CORD	INPUT SOCKET	WIRE COUNT	FREQUENCY (Hz)	VOLTAGE (V)	RATED AMPS (A)	MAX. CONT. AMPS (A)
-	IEC 60320 C20	1/N/PE, 2/PE	50/60	100-240	16	16

METERING PARAMETER	MEASUREMENT ACCURACY
VOLTAGE	±1 % + 0.1 VAC
CURRENT	±1.5 % + 0.01 A FROM 1 % TO 10 % OF UNIT RATING; ±1 % FROM >10 % TO 125 % OF UNIT RATING

RoHS COMPLIANT

 Dimensions in mm	Allgemeintoleranzen General tolerances		Oberfläche Finish	Werkstoff / Material	Gewicht: Weight: -
	-		-	-	-
	Drawn	04/11/15	Name	Bezeichnung / Description	
	Checked	04/11/15	Blass	MPH2-EBV_C20-16A_30N-60	
	Approved	-	Votýpka	Input and Branch Metered	
				Zeichnungs-Nr. / Drawing no.	Maßstab Scale
				MPHB1241	
Rev.	Change	Date	Name	Verwendet in / Used in	Blatt/Sheet
				-	1/1