


Disclosure and photocopying of this document, exploitation and communication of its contents are not permitted, unless permission is expressly granted. All rights are reserved.



CS8365C
 (50 A, 3/PE, 200-240 V)

OUTPUT POWER

BRANCH	PHASE	RECEPTACLE TYPE (QUANTITY)	VOLTAGE (V)	MAX. CONTINUOUS AMPS (A)	
				PER RECEPTACLE	PER BRANCH
A	L1-L2	4xC13, 1xC19	200-240	12/16	16
B	L2-L3	4xC13, 1xC19	200-240	12/16	16
C	L3-L1	4xC13, 1xC19	200-240	12/16	16
D	L1-L2	4xC13, 1xC19	200-240	12/16	16
E	L2-L3	4xC13, 1xC19	200-240	12/16	16
F	L3-L1	4xC13, 1xC19	200-240	12/16	16

AGENCY COMPLIANCE:
 - UL certification: UL 60950-1 (2nd), CSA C22.2 No. 60950-1-07
 - FCC certification
 - CB certification: IEC 60950-1 (2nd)

ENVIRONMENTAL RATING:
 OPERATING TEMPERATURE: 5 °C - 60 °C (41 °F - 140 °F) NON-CONDENSING, NON-CORROSIVE, 10 % - 90 % RH
 STORAGE TEMPERATURE: -20 °C - 85 °C (-4 °F - 185 °F)
 MAX. OPERATING ALTITUDE: 2000 m

- NOTES:**
- UNIT DIMENSIONS: 1826.5 mm (71.9") H x 50 mm (2.0") D x 56 mm (2.2") W
 - UNIT WEIGHT: 4 kg / 8.8 lbs
 - SHIPPING DIMENSIONS: 2017 mm (79.4") H x 297 mm (11.7") D x 176 mm (7.0") W
 - SHIPPING WEIGHT: 6.8 kg / 15 lbs
 - (2) MOUNTING BUTTONS AND (2) MOUNTING BRACKETS SUPPLIED WITH EACH UNIT. EITHER OPTION CAN BE USED TO MOUNT THE PDU.

INPUT POWER

INPUT CORD	INPUT PLUG	WIRE COUNT	FREQUENCY (Hz)	VOLTAGE (V)	RATED AMPS (A)	MAX. CONT. AMPS (A)
10 ft / 3 m	CS8365C	3/PE	50/60	200-240	50	40

METERING PARAMETER	MEASUREMENT ACCURACY
VOLTAGE	±1 % + 0.1 VAC
CURRENT	±1.5 % + 0.01 A FROM 1 % TO 10 % OF UNIT RATING; ±1 % FROM >10 % TO 125 % OF UNIT RATING

RoHS COMPLIANT

	Allgemeintoleranzen General tolerances		Oberfläche Finish	Werkstoff / Material	Gewicht / Weight: -
	-		-	-	-
Date		Name		Bezeichnung / Description	
03/11/15		Blass		MPH2-NBV_CS8365C_24N-60	
03/11/15		Votýpka		Input and Branch Metered	
-		-		Zeichnungs-Nr. / Drawing no.	
-		-		MPHB1724	
-		-		Maßstab Scale	
-		-		1:5	
-		-		Verwendet in / Used in	
-		-		Blatt/Sheet	
-		-		1/1	
Rev.	Change	Date	Name		
C	18131	06.06.2017	Petrů		

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts ist gestattet, soweit nicht ausdrücklich zugestanden. Alle Rechte vorbehalten.