



Disclosure and photocopying of this document, exploitation and communication of its contents are not permitted, unless permission is expressly granted. All rights are reserved.


FRONT VIEW



REAR VIEW



UPPER VIEW



OUTPUT POWER

BRANCH	PHASE	RECEPTACLE TYPE (QUANTITY)	VOLTAGE (V)	MAX. CONTINUOUS AMPS (A)	
				PER RECEPTACLE	PER BRANCH
A	L1-L2	1xC13, 2xC19	200-240	12/16	16
B	L2-L3	1xC13, 2xC19	200-240	12/16	16
C	L3-L1	2xC19	200-240	16	16
D	L1-L2	1xC13, 2xC19	200-240	12/16	16
E	L2-L3	1xC13, 2xC19	200-240	12/16	16
F	L3-L1	2xC19	200-240	16	16

METERING PARAMETER	MEASUREMENT ACCURACY
VOLTAGE	±1 % + 0.1 VAC
CURRENT	±1.5 % + 0.01 A FROM 1 % TO 10 % OF UNIT RATING; ±1 % FROM >10 % TO 125 % OF UNIT RATING

INPUT POWER

INPUT CORD	INPUT PLUG	WIRE COUNT	FREQUENCY (Hz)	VOLTAGE (V)	RATED AMPS (A)	MAX. CONT. AMPS (A)
10 ft / 3 m	CS8365C	3/PE	50/60	200-240	50	40



CS8365C
(50 A, 3/PE, 200-240 V)

AGENCY COMPLIANCE:

- UL certification: UL 60950-1 (2nd), CSA C22.2 No. 60950-1-07
- FCC certification
- CB certification: IEC 60950-1 (2nd)

ENVIRONMENTAL RATING:

OPERATING TEMPERATURE: 5 °C - 60 °C (41 °F - 140 °F) NON-CONDENSING, NON-CORROSIVE, 10 % - 90 % RH
 STORAGE TEMPERATURE: -20 °C - 85 °C (-4 °F - 185 °F)
 MAX. OPERATING ALTITUDE: 2000 m

NOTES:

- UNIT DIMENSIONS: 440 mm (17.3") W x 250 mm (9.8") D x 88 mm (3.5") H
- UNIT WEIGHT: 8 kg / 17,6 lbs
- SHIPPING DIMENSIONS: 543 mm (21.4") W x 485 mm (19.1") D x 240 mm (9.5") H
- SHIPPING WEIGHT: 8,5 kg / 18,7 lbs
- (2) MOUNTING BRACKETS SUPPLIED WITH EACH UNIT. BOTH SIDES CAN BE USED TO MOUNT THE PDU.

		Allgemeintoleranzen General tolerances		Oberfläche Finish		Werkstoff / Material		Gewicht: Weight: -	
		-		-		-		-	
Dimensions in mm		Drawn	19/05/16	Name		Bezeichnung / Description MPH2-NMC_CS8365C_4N-120 Input and Branch Metered + Outlet Metered			
		Checked	19/05/16	Racek					
		Approved	-	Votýpka					
Rev. Change Date Name				Zeichnungs-Nr. / Drawing no. MPHM6324		Maßstab Scale 1:5			
		Verwendet in / Used in -		Blatt/Sheet 1/1					

RoHS COMPLIANT

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Alle Rechte vorbehalten.