



Disclosure and photocopying of this document, exploitation and communication of its contents are not permitted, unless permission is expressly granted. All rights are reserved.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwendung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Alle Rechte vorbehalten.



AGENCY COMPLIANCE:
 - UL certification: UL 60950-1 (2nd), CSA C22.2 No. 60950-1-07
 - FCC certification
 - CB certification: IEC 60950-1 (2nd)
 - "-100" SUFFIX (PSE MODELS): INTERPRETATION OF DENAN TECHNICAL REQUIREMENTS MINISTERIAL ORDINANCE APPENDIX 12, J60950-1H26), J55022H22)

ENVIRONMENTAL RATING:
 OPERATING TEMPERATURE: 5 °C - 60 °C (41 °F - 140 °F) NON-CONDENSING, NON-CORROSIVE, 10 % - 90 % RH
 STORAGE TEMPERATURE: -20 °C - 85 °C (-4 °F - 185 °F)
 MAX. OPERATING ALTITUDE: 2000 m

- NOTES:
 1. UNIT DIMENSIONS: 1736.5 mm (68.4") H x 50 mm (2.0") D x 56 mm (2.2") W
 2. UNIT WEIGHT: 4 kg / 8.8 lbs
 3. SHIPPING DIMENSIONS: 2017.0 mm (79.4") H x 297 mm (11.7") D x 176 mm (7.0") W
 4. SHIPPING WEIGHT: 6.8 kg / 15 lbs
 5. (2) MOUNTING BUTTONS AND (2) MOUNTING BRACKETS SUPPLIED WITH EACH UNIT. EITHER OPTION CAN BE USED TO MOUNT THE PDU.

OUTPUT POWER

BRANCH	PHASE	RECEPTACLE TYPE (QUANTITY)	VOLTAGE (V)	MAX. CONTINUOUS AMPS (A)	
				PER RECEPTACLE	PER BRANCH
A	L1-L2	12xC13	200-240	12	16
B	L1-L2	12xC13	200-240	12	16

INPUT POWER

INPUT CORD	INPUT PLUG	WIRE COUNT	FREQUENCY (Hz)	VOLTAGE (V)	RATED AMPS (A)	MAX. CONT. AMPS (A)
10 ft / 3 m	NEMA L6-30P	2/PE	50/60	200-240	30	24

METERING PARAMETER	MEASUREMENT ACCURACY
VOLTAGE	±1 % + 0.1 VAC
CURRENT	±1.5 % + 0.01 A FROM 1 % TO 10 % OF UNIT RATING; ±1 % FROM >10 % TO 125 % OF UNIT RATING

RoHS COMPLIANT

 Dimensions in mm	Allgemeintoleranzen General tolerances		Oberfläche Finish	Werkstoff / Material	Gewicht: Weight: -
	-		-	-	-
Rev.	Change	Date	Name	Bezeichnung / Description MPH2-NRV_L6-30P_24N Input and Branch Metered + Outlet Metered/Switched	
B	18131	31.05.2017	Petrú	Zeichnungs-Nr. / Drawing no. MPHR1212	
				Maßstab Scale 1:5	
				Verwendet in / Used in -	
				Blatt/Sheet 1/1	