



Disclosure and photocopying of this document, exploitation and communication of its contents are not permitted, unless permission is expressly granted. All rights are reserved.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Alle Rechte vorbehalten.


REAR VIEW



SIDE VIEW



FRONT VIEW



OUTPUT POWER

BANK	PHASE	RECEPTACLE TYPE (QUANTITY)	VOLTAGE (V)	MAX. CONTINUOUS AMPS (A)	
				PER RECEPTACLE	PER BANK
A	L1	16xC13	100-240	10	16

INPUT POWER

INPUT CORD	INPUT SOCKET	WIRE COUNT	FREQUENCY (Hz)	VOLTAGE (V)	RATED AMPS (A)	MAX. CONT. AMPS (A)
-	IEC 60320 C20	1/N/PE, 2/PE	50/60	100-240	16	16

METERING PARAMETER	MEASUREMENT ACCURACY
VOLTAGE	±1 % + 0.1 VAC
CURRENT	±1.5 % + 0.01 A FROM 1 % TO 10 % OF UNIT RATING; ±1 % FROM >10 % TO 125 % OF UNIT RATING

RoHS COMPLIANT

AGENCY COMPLIANCE:

- UL certification: UL 60950-1 (2nd), CSA C22.2 No. 60950-1-07
- FCC certification
- CE-mark: LVD, EMC, RoHS (incl. harmonized standards hereunder)
- CB certification: IEC 60950-1 (2nd)
- BG certification: BV-BG (factory inspected)
- WEEE COMPLIANT

ENVIRONMENTAL RATING:

OPERATING TEMPERATURE: 5 °C - 60 °C (41 °F - 140 °F) NON-CONDENSING, NON-CORROSIVE, 10 % - 90 % RH  
 STORAGE TEMPERATURE: -20 °C - 85 °C (-4 °F - 185 °F)  
 MAX. OPERATING ALTITUDE: 2000 m

NOTES:

1. UNIT DIMENSIONS: 1004.5 mm (39.5") H x 50 mm (2.0") D x 56 mm (2.2") W
2. UNIT WEIGHT: 2.3 kg / 5.0 lbs
3. SHIPPING DIMENSIONS: 1197 mm (47.1") H x 218 mm (8.6") D x 137 mm (5.4") W
4. SHIPPING WEIGHT: 4.3 kg / 9.5 lbs
5. (2) MOUNTING BUTTONS AND (2) MOUNTING BRACKETS SUPPLIED WITH EACH UNIT. EITHER OPTION CAN BE USED TO MOUNT THE PDU.

<p>Dimensions in mm</p>	Allgemeintoleranzen General tolerances		Oberfläche Finish	Werkstoff / Material	Gewicht: Weight: -
	-		-	-	-
Drawn	11/02/16	Date		Name	
Checked	11/02/16	Date		Name	
Approved	-	Date		Name	
B	18131	30.05.217	Petrú	Bezeichnung / Description	
Rev.	Change	Date	Name	<p><b>MPH2-ERV_C20-16A_16N</b> Input and Branch Metered + Outlet Metered/Switched</p>	
				Zeichnungs-Nr. / Drawing no.	
				<p><b>MPHR3141</b></p>	
				Verwendet in / Used in	
				-	
				Maßstab Scale	
				1:5	
				Blatt/Sheet	
				1/1	