



Disclosure and photocopying of this document, exploitation and communication of its contents are not permitted, unless permission is expressly granted. All rights are reserved.


### FRONT VIEW



### REAR VIEW



### UPPER VIEW




### OUTPUT POWER

| BRANCH | PHASE | RECEPTACLE TYPE (QUANTITY) | VOLTAGE (V) | MAX. CONTINUOUS AMPS (A) |            |
|--------|-------|----------------------------|-------------|--------------------------|------------|
|        |       |                            |             | PER RECEPTACLE           | PER BRANCH |
| A      | L1    | 3x C13                     | 200-240     | 12                       | 16         |
| B      | L2    | 3x C13                     | 200-240     | 12                       | 16         |
| C      | L3    | 3x C13                     | 200-240     | 12                       | 16         |
| D      | L1    | 3x C13                     | 200-240     | 12                       | 16         |
| E      | L2    | 3x C13                     | 200-240     | 12                       | 16         |
| F      | L3    | 3x C13                     | 200-240     | 12                       | 16         |

| METERING PARAMETER | MEASUREMENT ACCURACY  |
|--------------------|---|
| VOLTAGE            | ±1 % + 0.1 VAC  |
| CURRENT            | ±1.5 % + 0.01 A FROM 1 % TO 10 % OF UNIT RATING;<br>±1 % FROM >10 % TO 125 % OF UNIT RATING |

### INPUT POWER

| INPUT CORD  | INPUT PLUG   | WIRE COUNT | FREQUENCY (Hz) | VOLTAGE (V)     | RATED AMPS (A) | MAX. CONT. AMPS (A) |
|-------------|--------------|------------|----------------|-----------------|----------------|---------------------|
| 10 ft / 3 m | NEMA L22-30P | 3/N/PE     | 50/60          | 200-240/346-415 | 30             | 24                  |



### AGENCY COMPLIANCE:

- UL certification: UL 60950-1 (2nd), CSA C22.2 No. 60950-1-07
- FCC certification
- CB certification: IEC 60950-1 (2nd)

### ENVIRONMENTAL RATING:

OPERATING TEMPERATURE: 5 °C - 60 °C (41 °F - 140 °F) NON-CONDENSING, NON-CORROSIVE, 10 % - 90 % RH  
 STORAGE TEMPERATURE: -20 °C - 85 °C (-4 °F - 185 °F)  
 MAX. OPERATING ALTITUDE: 2000 m

### NOTES:

- UNIT DIMENSIONS: 440 mm (17.3") W x 250 mm (9.8") D x 88 mm (3.5") H
- UNIT WEIGHT: 8 kg / 17.6 lbs
- SHIPPING DIMENSIONS: 543 mm (21.4") W x 485 mm (19.1") D x 240 mm (9.5") H
- SHIPPING WEIGHT: 8.5 kg / 18.7 lbs
- (2) MOUNTING BRACKETS SUPPLIED WITH EACH UNIT. BOTH SIDES CAN BE USED TO MOUNT THE PDU.

|                      |   |            |                      |  |                       |
|----------------------|---|------------|----------------------|--|-----------------------|
| <br>Dimensions in mm | Allgemeintoleranzen<br>General tolerances |            | Oberfläche<br>Finish | Werkstoff / Material                               | Gewicht:<br>Weight: - |
|                      | -   |            | -                    | -  | -                     |
|                      | Drawn                                     | 21/04/16   | Name                 | Bezeichnung / Description                          |                       |
|                      | Checked                                   | 21/04/16   | Racek                | MPH2-NRC_L22-30P_18N                               |                       |
|                      | Approved                                  | -          | Votýpka              | Input and Branch Metered + Outlet Metered/Switched |                       |
|                      | <br>VERTIV™                               |            |                      | Zeichnungs-Nr. / Drawing no.                       | Maßstab<br>Scale      |
|                      |   |            |                      | MPHR6131   |                       |
| Rev.                 | Change                                    | Date       | Name                 | Verwendet in / Used in                             | Blatt/Sheet           |
| B                    | 18154                                     | 13.06.2017 | Petrů                | -  | 1/1                   |

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Alle Rechte vorbehalten.