610 Executive Campus Drive
Westerville, OH 43082
FAX:
PH: (614) 841-5401

BILL OF MATERIAL

Siemens Medical Solutions

175 kVA PC System
EXMA175PMR1

Liebert EXM Power Conditioner System including: One (1) 175kVA Nameplate Liebert EXM UPS, model 51SA175TAA00HCS, with the following features:

- Fixed Capacity 175kVA / 175kW UPS System
- System Input Voltage of 480V, 60Hz, 3 Phase, 3 wire plus ground
- System Output Voltage of 480V, 60Hz, 3 Phase, 3 wire plus ground
- Single Input Configuration
- One (1) IntelliSlot Unity Dual Protocol Card; P/N: IS-UNITY-DP; Monitoring and configuration of Vertiv products and environmental sensors through stand-alone Web UI or integration with Trellis™, Liebert Nform, LIFE™ Services. Supports third-party management systems using SNMP, Modbus or BACnet.
- One (1) IS-RELAY Relay Contact Card
- 65kAIC Rating - Provides interrupting rating and labeling of 65kA
- Active Power Factor Corrected IGBT Input Converter
- PWM transistorized (IGBT) inverter
- Continuous Duty Static Bypass Switch
- Input Contacts - Dry contacts are available for functions including monitoring external breakers, on-generator signal, and other functions
- Output Contacts - Dry contacts are available for functions including a permissive signal to maintenance bypass SKRU, to trip external breakers, and other functions
- Generator Load Control - Suppresses battery charging reducing power demand by an external signal. Shifts unit from Eco Mode to double conversion (if applicable), and synchronizes the inverter output with the bypass
- DSP based controls - Provides digital control of power conversion and system operation
- Backlit LCD display - Monitors power conversion, UPS operation and utility conditions. Deviations are logged for troubleshooting
- Temperature-Compensated Charging/Battery Load Test
- Bottom cable entry to UPS, top cable entry through matching bypass or optional wiring cabinet
- Front only service access
- Local Emergency Power Off (EPO)
- LIFE™ Services for the 1st year
- IP 20 enclosure
- Casters and leveling feet
- UL and cUL Listed to UL Standard 1778 5th Edition
- Liebert EXM Factory Services Certified Test Report

The system includes **One (1) Maintenance Bypass Matching Cabinet(s), model 51MBT33AA0R0HCS** with the following features:

- 3 Switching Devices (BIB,MBB,MIB)
- Padlock Provisions for Breakers MBB and MIB
- 300 Amp Breaker Trip Rating
- Cabinet Mounted Right Attached to Module with connecting cables factory supplied
- Cabinet ships attached to the UPS Module
- 300 MM - 11.8 inches Frame Size
- Front Access service design


System Startup Services

Startup includes one site trip by a LS customer engineer after the UPS has been installed. The site trip includes the following services for one UPS module: non-powered inspection, UPS electrical and operational checkout, full parts and labor for any remedial work required on the UPS or battery cabinets, and customer operation training. Startup also includes remedial onsite labor, parts, and travel for the full warranty period.

- Startup 24x7 is scheduled at the customers designated time
- MBC/BDC/Wallmount Panel Startup is included

Optional Accessories (If Included in Order)

- Seismic Anchor Kits for UPS Module and Maintenance Bypass Cabinet Where Applicable
- Remote Monitoring Panel



BIB - BYPASS ISOLATION BREAKER

MBB - MAINTENANCE BYPASS BREAKER

MIB - MAINTENANCE ISOLATION BREAKER

* EXTERNAL OVERCURRENT PROTECTION BY OTHERS

FIELD SUPPLIED WIRING

NOTES:
1. INSTALL IN ACCORDANCE WITH NATIONAL AND LOCAL ELECTRICAL CODES.
2. INPUT AND BYPASS MUST SHARE THE SAME SINGLE SOURCE.
3. GROUNDING CONDUCTORS ARE REQUIRED.
4. BYPASS AND RECTIFIER INPUTS AND OUTPUT CABLES MUST BE RUN IN SEPARATE CONDUITS.
5. CONTROL WIRING MUST BE RUN IN SEPARATE CONDUITS.

DRAWN BY K. STACY	SHEET NO. 1 OF 1	ONE-LINE DIAGRAM SINGLE INPUT 50kVA - 250kVA WITH 3 BREAKER MAINTENANCE BYPASS CABINET LIEBERT 480VAC eXM				VERTIV.
CHK BY M. ROCKWELL	ECN NO.					
REF. DWG.	ORDER NO.		DWG. NO. EXM41011	DATE 10/21/15	REV. # 0	1050 DEARBORN DRIVE P.O. BOX 29186 COLUMBUS, OHIO 43229

FILE NAME: I:\appl\Ohio Appl\AE Submittals - Standard\eXM dwg\480V\A) One-Line Diagram\EXM41011-00.dwg

ELECTRICAL DATA									
kVA RATINGS	VOLTAGE		AC INPUT CURRENT "A"			BATTERY		AC OUTPUT CURRENT "A"	
	INPUT	OUTPUT	NOM.	MAX	REC. OPD	NOM. VDC	MAX. DISCHARGE, A	NOM.	REC. OPD
30	480	480	38	42	60	432	87	36	50
40	480	480	50	56	70	432	116	48	60
50	480	480	63	69	90	432	145	60	80
75	480	480	94	104	150	432	218	90	125
100	480	480	126	138	175	432	290	120	150
125	480	480	157	173	225	432	363	150	200
150	480	480	189	208	300	432	435	180	225
175	480	480	220	243	350	432	508	210	300
200	480	480	252	277	350	432	581	241	300
225	480	480	284	312	400	432	654	271	350
250	480	480	315	346	450	432	726	301	400

HEAT / WEIGHT INFORMATION			
kVA RATINGS	HEAT	WEIGHT PACKAGED, LBS (KG)	
	UPS (BTU/HR)	200kVA FRAME	250kVA FRAME
30	4,712	748 (339)	868 (394)
40	6,283	748 (339)	868 (394)
50	7,854	748 (339)	868 (394)
75	10,388	842 (382)	962 (436)
100	13,851	842 (382)	962 (436)
125	15,015	936 (425)	1056 (479)
150	18,019	936 (425)	1056 (479)
175	22,242	1030 (467)	1150 (522)
200	25,491	1030 (467)	1150 (522)
225	31,164	N/A	1244 (564)
250	34,627	N/A	1244 (564)

THIS CHART IS FOR UPS WEIGHTS ONLY. FOR MBC OR BDC WEIGHTS REFER TO SUBMITTAL EXM18014 OR EXM18015.

NOTES

1. NOMINAL INPUT CURRENT (CONSIDERED CONTINUOUS) IS BASED ON FULL RATED OUTPUT LOAD. MAXIMUM CURRENT INCLUDES NOMINAL INPUT CURRENT AND MAXIMUM BATTERY RECHARGE CURRENT (CONSIDERED NONCONTINUOUS). CONTINUOUS AND NONCONTINUOUS CURRENT ARE DEFINED IN NEC 100. RECOMMENDED OVERCURRENT PROTECTION IS BASED ON 80% RATED DEVICES. * THE RECOMMENDED OVERCURRENT PROTECTION REPRESENTS 125% OF NOMINAL FULL LOAD CURRENT (CONTINUOUS) PER NEC 215.
2. MAXIMUM INPUT CURRENT IS CONTROLLED BY THE CURRENT LIMIT SETTING.
3. RECOMMENDED AC INPUT EXTERNAL OVERCURRENT PROTECTION IS BASED ON 80% RATED DEVICES AND MAXIMUM INPUT CURRENT LIMIT SETTING.
4. RECOMMENDED AC OUTPUT EXTERNAL OVERCURRENT PROTECTION IS BASED ON 80% RATED DEVICES AND FULL RATED OUTPUT CURRENT.
5. NOMINAL BATTERY VOLTAGE IS SHOWN AT 2.0 VOLTS / CELL.
6. INPUT POWER FACTOR OF 0.99 IS USED FOR THE CALCULATIONS.

SHEET NO.: 1 OF 1	DRAWN BY: J. SHIPMAN	TITLE: TECHNICAL INFORMATION 50-250kVA, 60Hz, 480VAC IN, 480VAC OUT SINGLE INPUT LIEBERT 480VAC EXM	DWG. NO.: EXM48001	VERTIV.
ECN NO.:	DESIGNED BY: D. HUDSON		DATE (LATEST REV.): 06/04/2018	
REF DWG.:	APPROVED BY: D. HUDSON		REVISION: 5	1050 DEARBORN DR P.O. BOX 29186 COLUMBUS, OH 43229

2-Breaker MBC Circuit Breaker Schedule							
KVA Rating	MIB/MBB						
	AF/AT	Ir	Isd	Ii/Im	MFG	MFG PN	KAIC
50	150/80	Fixed	NA	10	Square D	HJF36080YE	65
100	150/150	Fixed	NA	10	Square D	HJF36150YE	65
150	250/225	Fixed	NA	10	Square D	JJF36225YE	65
200	400/300	300	1.5	9	Square D	LJF36400TU33XTW	65
250	400	400	1.5	10	Square D	LJF36400TU33XTW	65

WEIGHT INFORMATION		
MBC WIDTH	kVA RATING	WEIGHT lb (kg)
200mm	50-100	195 (90)
300mm	150-250	288 (131)
300mm W/CHOKE	50-100	408 (185)
600mm W/CHOKE	150-250	649 (295)


3-Breaker MBC Circuit Breaker Schedule														
KVA Rating	BIB							MIB/MBB						
	AF/AT	Ir	Isd	Ii/Im	MFG	MFG PN	KAIC	AF/AT	Ir	Isd	Ii/Im	MFG	MFG PN	KAIC
50	150/90	Fixed	NA	10	Square D	HJF36090YE	65	150/80	Fixed	NA	10	Square D	HJF36080YE	65
100	250/175	Fixed	NA	10	Square D	JJF36175TYE	65	150/150	Fixed	NA	10	Square D	HJF36150YE	65
150	400/300	300	1.5	9	Square D	LJF36400TU33XTW	65	250/225	Fixed	NA	10	Square D	JJF36225YE	65
200	400/350	350	1.5	10	Square D	LJF36400TU33XTW	65	400/300	300	1.5	9	Square D	LJF36400TU33XTW	65
250	600/450	450	1.5	8	Square D	LJF36600TU33XTW	65	400	400	1.5	10	Square D	LJF36400TU33XTW	65
175	400/350	350	1.5	10	Square D	LJF36400U33X	65	400/300	300	1.5	10	Square D	LJF36400U33X	65

4-Breaker MBC Circuit Breaker Schedule																						
KVA Rating	RIB							BIB							MIB/MBB							
	AF/AT	Ir	Isd	Ii/Im	MFG	MFG PN	KAIC	AF/AT	Ir	Isd	Ii/Im	MFG	MFG PN	KAIC	AF/AT	Ir	Isd	Ii/Im	MFG	MFG PN	KAIC
50	150/90	Fixed	NA	10	Square D	HJF36090YE	65	150/80	Fixed	NA	10	Square D	HJF36080YE	65	150/80	Fixed	NA	10	Square D	HJF36080YE	65
100	250/175	Fixed	NA	10	Square D	JJF36175TYE	65	150/150	Fixed	NA	10	Square D	HJF36150YE	65	150/150	Fixed	NA	10	Square D	HJF36150YE	65
150	400/300	300	1.5	9	Square D	LJF36400TU33XTW	65	250/225	Fixed	NA	10	Square D	JJF36225YE	65	250/225	Fixed	NA	10	Square D	JJF36225YE	65
200	400/350	350	1.5	10	Square D	LJF36400TU33XTW	65	400/300	300	1.5	9	Square D	LJF36400TU33XTW	65	400/300	300	1.5	9	Square D	LJF36400TU33XTW	65
250	600/450	450	1.5	8	Square D	LJF36600TU33XTW	65	400	400	1.5	10	Square D	LJF36400TU33XTW	65	400	400	1.5	10	Square D	LJF36400TU33XTW	65

SHEET NO.: 1 OF 1	DRAWN BY: K. STACY	TITLE: TECHNICAL INFORMATION MAINTENANCE BYPASS CABINETS (MBC) LIEBERT 480VAC EXM	DWG. NO.: EXM48004
ECN NO.:	DESIGNED BY: D. McLAURIN		DATE (LATEST REV.): 8/9/2017
REF DWG.:	APPROVED BY: D. McLAURIN		REVISION: 2

1050 DEARBORN DR
P.O. BOX 29186
COLUMBUS, OH 43229

VERTIV.




FRONT VIEW

NOTES:


1. ALL DIMENSIONS ARE IN inches [mm].
2. 24" [610] MINIMUM CLEARANCE ABOVE UNIT FOR AIR EXHAUST. 36" [914] FRONT ACCESS REQUIRED FOR SERVICE.
3. KEEP CABINET WITHIN 15 DEGREES OF VERTICAL.
4. UPS – BOTTOM CABLE ENTRY THROUGH REMOVABLE PLATES. MBC – TOP AND BOTTOM ENTRY THROUGH REMOVABLE PLATES. REMOVE, PUNCH TO SUIT CONDUIT SIZE AND REPLACE.
5. UNIT BOTTOM IS STRUCTURALLY ADEQUATE FOR FORKLIFT HANDLING.
6. CONTROL WIRING AND POWER WIRING MUST BE RUN IN SEPARATE CONDUITS.
7. ALL WIRING IS TO BE IN ACCORDANCE WITH NATIONAL AND LOCAL ELECTRICAL CODES.
8. ALL BATTERY CABINETS MUST BE POSITIONED ON THE LEFT SIDE OF UPS.

DRAWN BY K. STACY	SHEET NO. 1 OF 1	LINE-UP DETAIL 150kVA - 200kVA UPS TO MAINTENANCE BYPASS CABINET (300mm) LIEBERT 480VAC EXM				VERTIV.
CHK BY L. BRAZIS	ECN NO.					
REF. DWG.	ORDER NO.		DWG. NO. EXM43013	DATE 1/15/16	REV. # 1	1050 DEARBORN DRIVE P.O. BOX 29186 COLUMBUS, OHIO 43229


FILE NAME: I:\appl\Ohio Appl\AE Submittals - Standard\eXM dwg\480V\C) Line-Up Detail\EXM43013-01.dwg




TOP VIEW



BOTTOM VIEW




FRONT VIEW



RIGHT SIDE VIEW

NOTES:
1. ALL DIMENSIONS ARE IN inches [mm].
2. 24" [610] MINIMUM CLEARANCE ABOVE UNIT AIR EXHAUST. 36" [914] FRONT ACCESS REQUIRED FOR SERVICE.
3. KEEP CABINET WITHIN 15 DEGREES OF VERTICAL.
4. BOTTOM CABLE ENTRY AVAILABLE THROUGH REMOVABLE ACCESS PLATES. REMOVE, PUNCH TO SUIT CONDUIT SIZE AND REPLACE.
5. UNIT BOTTOM IS STRUCTURALLY ADEQUATE FOR FORKLIFT HANDLING.
6. CONTROL WIRING AND POWER WIRING MUST BE RUN IN SEPARATE CONDUITS.
7. ALL WIRING IS TO BE IN ACCORDANCE WITH NATIONAL AND LOCAL ELECTRICAL CODES.
8. OVERALL DIMENSIONS ARE SHOWN WITH SIDE PANELS.



DETAIL A


UPS kVA RATING	CENTER OF GRAVITY (mm)		
	X	Y	Z
50	12.00"(305mm)	33.47"(850mm)	18.90"(480mm)
100	12.00"(305mm)	37.40"(950mm)	18.90"(480mm)
150	12.00"(305mm)	41.34"(1050mm)	18.90"(480mm)
200	12.00"(305mm)	45.27"(1150mm)	18.90"(480mm)

DRAWN BY J. SHIPMAN	SHEET NO. 1 OF 2	OUTLINE DRAWING 50kVA - 200kVA UPS LIEBERT 480VAC EXM			
CHK BY B. SANBORN	ECN NO.				
REF. DWG.	ORDER NO.		DWG. NO. EXM42001A	DATE 4/6/18	REV. # 3


VERTIV.

1050 DEARBORN DRIVE
P.O. BOX 29186
COLUMBUS, OHIO 43229


FILE NAME: I:\appl-DLW\Ohio Appl\AE Submittals - Standard\eXM dwg\480V\B) Outline Dwg\EXM42001A-03.dwg



DETAIL A



FRONT VIEW
WITH DOOR OPENED



RIGHT SIDE VIEW
WITH DOOR OPENED
(AND SIDE PANEL REMOVED)

DRAWN BY J. SHIPMAN	SHEET NO. 2 OF 2
CHK BY B. SANBORN	ECN NO.
REF. DWG.	ORDER NO.


OUTLINE DRAWINGS
MAIN COMPONENTS LAYOUT
50kVA - 200kVA UPS
LIEBERT 480VAC EXM

DWG. NO.	DATE	REV. #
EXM42001B	4/6/18	3


1050 DEARBORN DRIVE
P.O. BOX 29186
COLUMBUS, OHIO 43229

VERTIV.

FILE NAME: I:\appl-DLW\Ohio Appl\AE Submittals - Standard\eXM dwg\480V\B) Outline Dwg\EXM42001B-03.dwg




TOP VIEW




BOTTOM VIEW

NOTES:
1. ALL DIMENSIONS ARE IN inches [mm].
2. 24" [610] MINIMUM CLEARANCE ABOVE UNIT FOR AIR EXHAUST. 36" [914] FRONT ACCESS REQUIRED FOR SERVICE.
3. KEEP CABINET WITHIN 15 DEGREES OF VERTICAL.
4. UPS – BOTTOM CABLE ENTRY THROUGH REMOVABLE PLATES. MBC – TOP AND BOTTOM CABLE ENTRY THROUGH REMOVABLE PLATES. REMOVE, PUNCH TO SUIT CONDUIT SIZE AND REPLACE.
5. UNIT BOTTOM IS STRUCTURALLY ADEQUATE FOR FORKLIFT HANDLING.
6. CONTROL WIRING AND POWER WIRING MUST BE RUN IN SEPARATE CONDUITS.
7. ALL WIRING IS TO BE IN ACCORDANCE WITH NATIONAL AND LOCAL ELECTRICAL CODES.
8. UPS SHOWN FOR REFERENCE ONLY. REFER TO OUTLINE DRAWING OF YOUR UPS FOR ACCURATE DIMENSIONS.
9. OVERALL DIMENSIONS ARE SHOWN WITH SIDE PANELS.




FRONT VIEW
(SEE NOTE 8)



RIGHT SIDE VIEW

UPS kVA RATING	CENTER OF GRAVITY in(mm)			NOTE
	X	Y	Z	
150	16 (406)	46 (1168)	16.1 (408)	WITH MBC
200	16 (406)	46 (1168)	16.1 (408)	WITH MBC




DETAIL A

DRAWN BY K. STACY	SHEET NO. 1 OF 2	OUTLINE DRAWING 150kVA - 200kVA 2-4 BREAKER MAINTENANCE BYPASS CABINET (300mm) LIEBERT 480VAC EXM			
CHK BY J. SHIPMAN	ECN NO.				
REF. DWG.	ORDER NO.		DWG. NO. EXM42007A	DATE 3/17/17	REV. # 1


VERTIV.

1050 DEARBORN DRIVE
P.O. BOX 29186
COLUMBUS, OHIO 43229


FILE NAME: I:\appl-DLW\Ohio Appl\AE Submittals - Standard\eXM dwg\480V\B) Outline Dwg\EXM42007A-01.dwg



LEFT SIDE VIEW
WITH PANEL REMOVED



FRONT VIEW
WITH DOOR REMOVED



RIGHT SIDE VIEW
WITH PANEL REMOVED

NOTES:
1. 2–BREAKER MBC CONSISTS OF MBB AND MIB.

2. 3–BREAKER MBC CONSISTS OF MBB, MIB, AND BIB.


3. 4–BREAKER MBC CONSISTS OF MBB, MIB, BIB, AND RIB.

DRAWN BY K. STACY	SHEET NO. 2 OF 2	OUTLINE DRAWING MAIN COMPONENTS LAYOUT 150kVA - 200kVA 2-4 BREAKER MAINTENANCE BYPASS CABINET (300mm) LIEBERT 480VAC EXM			VERTIV. 1050 DEARBORN DRIVE P.O. BOX 29186 COLUMBUS, OHIO 43229
CHK BY J. SHIPMAN	ECN NO.				
REF. DWG.	ORDER NO.		DWG. NO. EXM42007B	DATE 3/17/17	REV. # 1


FILE NAME: I:\appl-DLW\Ohio Appl\AE Submittals - Standard\eXM dwg\480V\B) Outline Dwg\EXM42007B-01.dwg

NOTES:
1. ALL DIMENSIONS ARE IN inches [mm].
2. CONTROL WIRING AND POWER WIRING MUST BE RUN IN SEPARATE CONDUITS.
3. ALL WIRING IS TO BE IN ACCORDANCE WITH NATIONAL AND LOCAL ELECTRICAL CODES.


TERMINAL SPECIFICATIONS			
UNIT RATING	UTILITY CONFIGURATIONS		
	BOLT SHAFT SIZE	TORQUE	
		LB-IN	N-M
50-200	M12	428	48




FRONT VIEW
WITH DOOR REMOVED




RIGHT SIDE VIEW
WITH PANEL REMOVED




DETAIL A



DETAIL B
(RECTIFIER AND BYPASS INPUT BUSBARS)



DETAIL C
(BATTERY AND OUTPUT BUSBARS)



GROUND BUSBAR


DRAWN BY K. STACY	SHEET NO. 1 OF 1	TERMINAL DETAIL 50kVA - 200kVA UPS LIEBERT 480VAC EXM			
CHK BY L. BRAZIS	ECN NO.				
REF. DWG.	ORDER NO.		DWG. NO. EXM46001	DATE 1/21/16	REV. # 1

1050 DEARBORN DRIVE
P.O. BOX 29186
COLUMBUS, OHIO 43229


VERTIV.

FILE NAME: I:\appl\Ohio Appl\AE Submittals - Standard\eXM dwg\F) Terminal Details\EXM46001-01.dwg


NOTES:
1. ALL DIMENSIONS ARE IN inches [mm].
2. CONTROL WIRING AND POWER WIRING MUST BE RUN IN SEPARATE CONDUITS.
3. ALL WIRING IS TO BE IN ACCORDANCE WITH NATIONAL AND LOCAL ELECTRICAL CODES.
4. IF MAINTENANCE BYPASS CABINET IS ATTACHED TO UPS, LIEBERT WILL SUPPLY THE INTERCONNECTION CABLES.




LEFT SIDE VIEW
WITH PANEL REMOVED




FRONT VIEW
WITH DOOR REMOVED



RIGHT SIDE VIEW
WITH PANEL REMOVED



DETAIL A




GROUND BUSBAR

DRAWN BY K. STACY	SHEET NO. 1 OF 1	TERMINAL DETAIL 3 BREAKER MAINTENANCE BYPASS CABINET (300mm) FOR USE WITH 150kVA - 250kVA UPS LIEBERT 480VAC EXM			VERTIV.
CHK BY M. ROCKWELL	ECN NO.				
REF. DWG.	ORDER NO.				
		DWG. NO. EXM46009	DATE 12/2/15	REV. # 0	1050 DEARBORN DRIVE P.O. BOX 29186 COLUMBUS, OHIO 43229

FILE NAME: I:\appl\Ohio Appl\AE Submittals - Standard\eXM dwg\480V\F) Terminal Details\EXM46009-00.dwg

NOTES:
1. ALL DIMENSIONS ARE IN inches [mm].
2. UNIT BOTTOM IS STRUCTURALLY ADEQUATE FOR FORKLIFT HANDLING




FRONT
(VIEWED LOOKING TOP DOWN)

DRAWN BY K. STACY	SHEET NO. 1 OF 1	BASE DETAIL 50kVA - 200kVA UPS LIEBERT 480VAC EXM				VERTIV.
CHK BY L. BRAZIS	ECN NO.					
REF. DWG.	ORDER NO.		DWG. NO. EXM49001	DATE 2/25/16	REV. # 1	1050 DEARBORN DRIVE P.O. BOX 29186 COLUMBUS, OHIO 43229

FILE NAME: I:\appl\Ohio Appl\AE Submittals - Standard\eXM dwg\I) Seismic & Base Details\EXM08001-01.dwg

NOTES:
1. ALL DIMENSIONS ARE IN inches [mm].
2. UNIT BOTTOM IS STRUCTURALLY ADEQUATE FOR FORKLIFT HANDLING



FRONT
(VIEWED LOOKING TOP DOWN)

DRAWN BY J. SHIPMAN	SHEET NO. 1 OF 1	BASE DETAIL MAINTENANCE BYPASS CABINET (300mm) LIEBERT 480VAC EXM				VERTIV.
CHK BY J. SHIPMAN	ECN NO.					
REF. DWG.	ORDER NO.		DWG. NO. EXM49005	DATE 1/31/18	REV. # 0	1050 DEARBORN DRIVE P.O. BOX 29186 COLUMBUS, OHIO 43229


FILE NAME: I:\appl\Ohio Appl\AE Submittals - Standard\eXM dwg\480V\I) Seismic & Base Details\EXM49005-01.dwg

CABLE GROUP #10A - MIB/MBB AUX CONTACTS								
TERMINAL DESIGNATION		COLOR	SIGNAL NAME	MAXIMUM VOLTAGE	MAXIMUM CURRENT	UPS TERMINATION WIRE RANGE	MAXIMUM LENGTH	REMARKS
FROM	TO							
TB1-3	X9J26-9	BLACK	MBB STATUS	30VDC/ 250VAC	8A	#16-20AWG	200FT	
TB1-4	X9J26-11	WHITE	GROUND					
TB1-5	X9J26-13	BLACK	MIB STATUS					
TB1-6	X9J26-15	WHITE	GROUND					
CABLE GROUP #10B - BIB SHUNT TRIP								
TERMINAL DESIGNATION		COLOR	SIGNAL NAME	MAXIMUM VOLTAGE	MAXIMUM CURRENT	UPS TERMINATION WIRE RANGE	MAXIMUM LENGTH	REMARKS
FROM	TO							
TB1-7	X9J23-3	RED	BFP_S	30VDC/ 480VAC	4A	#16-20AWG	200FT	
X9J23-1	F5/F7	BLACK	BFP_O					
TB1-8	F6/F8	BLACK	SHUNT TRIP					
CABLE GROUP #10C - RIB SHUNT TRIP								
TERMINAL DESIGNATION		COLOR	SIGNAL NAME	MAXIMUM VOLTAGE	MAXIMUM CURRENT	UPS TERMINATION WIRE RANGE	MAXIMUM LENGTH	REMARKS
FROM	TO							
TB1-10	X9J24-3	RED	MFP_S	30VDC/ 480VAC	4A	#16-20AWG	200FT	
X9J24-1	F5/F7	BLACK	MFP_O					
TB1-9	F6/F8	BLACK	SHUNT TRIP					
CABLE GROUP #10D - UPS ON BYPASS								
TERMINAL DESIGNATION		COLOR	SIGNAL NAME	MAXIMUM VOLTAGE	MAXIMUM CURRENT	UPS TERMINATION WIRE RANGE	MAXIMUM LENGTH	REMARKS
FROM	TO							
TB1-11	X9J23-6	BLACK	INV_C	30VDC/ 250VAC	8A	#16-20AWG	200FT	
TB1-12	X9J23-4	WHITE	INV_S					


SHEET NO.: 1 OF 1	DRAWN BY: J. SHIPMAN	TITLE: CONTROL WIRING CABLE GROUP #10 UPS TO MAINTENANCE BYPASS CABINET (MBC) LIEBERT 480VAC EXM	DWG. NO.: EXM44015	VERTIV™
ECN NO.:	DESIGNED BY: G. HOGE		DATE (LATEST REV.): 11/29/2017	
REF DWG.:	APPROVED BY: G. HOGE		REVISION: 4	1050 DEARBORN DR P.O. BOX 29186 COLUMBUS, OH 43229


— — FIELD SUPPLIED WIRING

SINGLE EXM MODULE



THREE MODULES IN PARALLEL





EXM BYPASS MODULE

DRAWN BY K. STACY	SHEET NO. 1 OF 1	WIRING DIAGRAM REMOTE EPO 50kVA - 250kVA LIEBERT 480VAC EXM			
CHK BY N. JENKINS	ECN NO.				
REF. DWG.	ORDER NO.		DWG. NO. EXM44016	DATE 5/3/16	REV. # 0


VERTIV™

1050 DEARBORN DRIVE
P.O. BOX 29186
COLUMBUS, OHIO 43229

FILE NAME: I:\appl-DLW\Ohio Appl\AE Submittals - Standard\eXM dwg\480V\D) Power & Control Wiring\EXM44016-00.dwg

NOTES

1. NO LOAD POWER LOSS: 1.48 kW



ECO MODE


NORMAL MODE

SHEET NO.: 1 OF 1	DRAWN BY: J. SHIPMAN	TITLE: UPS EFFICIENCY 200 kVA LIEBERT 480VAC EXM	DWG. NO.: EXM47009	VERTIV™
ECN NO.:	DESIGNED BY: B. SANBORN		DATE (LATEST REV.): 12/06/2018	
REF DWG.:	APPROVED BY: B. SANBORN		REVISION: 0	1050 DEARBORN DR P.O. BOX 29186 COLUMBUS, OH 43229

LIEBERT® INTELLISLOT™ CARDS
Product Specification/Installation Guide

VERTIV™

Liebert® IntelliSlot Web Card



INTELLISLOT™ WEB CARD FAMILY

- Liebert® IntelliSlot Web Card
- Liebert® IntelliSlot Web Card-LB
- Liebert® IntelliSlot WebCard-LBDS

The Liebert IntelliSlot Web Card family delivers enhanced communications and control to Liebert UPS, Power Management and Precision Cooling systems.

Liebert IntelliSlot Web cards bring SNMP, Telnet and Web-management capability to many models of Liebert UPS, power and cooling equipment. The cards employ an Ethernet network to monitor and manage a wide range of operating parameters, alarms and notifications.

ADDITIONAL FEATURES

- SNMPv1, SNMPv2c and with MIB-II support
- HTTP/HTTPS 1.1
- Telnet
- BootP, DHCP per RFC2131/2132
- Remote sockets
- Remote firmware updates via HTTP


COMPATIBILITY with Liebert Equipment

IntelliSlot Web Card	Part Number	Compatible with:		
Liebert IntelliSlot Web Card	IS-WEBCARD	• Liebert PowerSure PSI™ • Liebert GXT™	• Liebert GXT™ 6kVA • Liebert GXT™ 6kVA	• Liebert GXT2U™ • Liebert Nfinity®
Liebert IntelliSlot Web Card-LB	IS-WEBLB	• Liebert NX™	• Liebert Hinet™	
Liebert IntelliSlot Web Card-LBDS	IS-WEBLBDS	• Liebert DS™ Precision Cooling Unit		

COMPATABILITY with Communication Protocols

IntelliSlot Web Card	Part Number	Compatible with:					
		SNMP	HTTP	HTTPS	EMAIL	SMS	TELNET
Liebert IntelliSlot Web Card	IS-WEBCARD	✓	✓	✓	✓	✓	✓
Liebert IntelliSlot Web Card-LB	IS-WEBLB	✓	✓	✓	✓	✓	✓
Liebert IntelliSlot Web Card-LBDS	IS-WEBLBDS	✓	✓	—	—	—	✓

DIMENSIONS



SPECIFICATIONS

Power Requirements	AC Inputs	18 - 24 VAC; 50/60 Hz
	DC Inputs	12 - 36VDC
	Power Consumptions:	6VA maximum (1.75W)
Dimensions, W x D x H	3 x 5-1/4 x 2-3/8 (76 x 134 x 38 mm)	
Weight (assembled)	Net:	7 oz (0.2 kg)
	Shipping:	1.3 lb (0.6 kg)
Ambient Operating Environment	32 to 104°F (0 to 40°C); 10% to 90% RH (non-condensing)	
Ambient Storage Temperature	–4 to 140°F (–20 to 60°C)	
Protection	SELV Isolated User Connections, Watchdog Timer Circuitry	
Communication Ports	Service Terminal (RS-232)	DB9F, DTE
	Ethernet Communications	RJ45

WIRING


Connection	Supported Wire Type	Max. Wire Length
1RS-232	Null Modem Cable	50 ft. (15.3m)
DB9F Connector	DTE Null Modem Cable	50 ft. (15m)
RJ45 Connector	Standard Category 5 Cable	328 ft. (100m)

To contact Vertiv Technical Support: visit www.VertivCo.com

© 2017 Vertiv Co. All rights reserved. Vertiv and the Vertiv logo are trademarks or registered trademarks of Vertiv Co. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness herein, Vertiv Co. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications are subject to change without notice.

LIEBERT® INTELLISLOT™ UNITY PLATFORM CARDS

Product Specification/Installation Guide



The Liebert IntelliSlot Unity Platform brings SNMP, BACnet IP, BACnet MSTP, Modbus TCP, Modbus RTU, YDN23 and Web management capability to many models of Vertiv's power and cooling equipment. The cards employ Ethernet and RS-485 networks to monitor and manage a wide range of operating parameters, alarms and notifications. The card also supports communication for LIFE™ Services by VERTIV.

ADDITIONAL FEATURES

- SNMPv1, SNMPv2c and SNMPv3 with MIB-II support
- HTTP/HTTPS 1.1
- BootP
- DHCP per RFC2131/2132
- Remote firmware updates via a Web browser
- IPv6 support for HTTP/HTTPS, DHCPv6, e-mail, SMS, SNMP v1/v2c/v3 and Modbus TCP
- Liebert SN Environmental Sensor Support (Web, SNMP, SMS and SMTP): Temperature, Humidity, Door Closure, Contact Closure and Leak Detection: Liebert SN-2D, Liebert SN-3C, Liebert SN-L, Liebert SN-T, Liebert SN-TH, Liebert SN-Z01, Liebert SN-Z02 and Liebert SN-Z03

IntelliSlot Unity cards are a form, fit, and function replacement for several Liebert IntelliSlot Web and 485 cards.

COMPATABILITY with Liebert Equipment

IntellSlot Card	Compatible with			
IS-UNITY-DP IS-UNITY-SNMP IS-UNITY-LIFE	Alber BDSU-50™	Liebert Deluxe System/3™	Liebert GXT3™	Liebert PeX™ *
	Liebert APM™	Liebert DS™	Liebert GXT4™	Liebert PPC™
	Liebert APS™	Liebert DSE™	Liebert HPC™	Liebert RDC™
	Liebert Challenger 3000™	Liebert EPM™	Liebert HPC-S/M/R/W/Generic™	Liebert RX™
		Liebert EXC™	Liebert HPM™	Liebert XDC™
	Liebert CRV™	Liebert eXL™	Liebert NX™ 225-600 kVA	Liebert XDP™
	Liebert CW™	Liebert EXL™ S1	Liebert NXC™	Liebert XDP-Cray™
	Liebert DCL™	Liebert eXM™	Liebert NXL™ *	
	Liebert DCP™	Liebert FDC™	Liebert NXR™	
		Liebert FPC™	Liebert PCW™/PDX™	


** YDN23 supported only for Liebert PeX and Liebert NXL.*

COMPATABILITY with Communication Protocols


Liebert IntelliSlot Card	Life Services Support	Communication Protocol							
		HTTP HTTPS	Velocity Protocol	Email	SMS	SNMP v1, v2c, v3	BACnet IP BACnet MSTP	Modbus TCP Modbus RTU	YDN23*
IS-UNITY-DP	✓	✓	✓	✓	✓	✓	✓	✓	✓
IS-UNITY-SNMP	✓	✓	✓	✓	✓	✓	—	—	—
IS-UNITY-LIFE	✓	✓	✓	✓	✓	—	—	—	—

* YDN23 supported only for Liebert PeX and Liebert NXL.

DIMENSIONS



Front face



Board

SPECIFICATIONS

Power Requirements	DC Inputs	7 to 12 VDC
	Power Consumptions:	3.6 W maximum
Dimensions, W x D x H	2.97 x 5.2 x 1.45 in. (75.5 x 15 x 37 mm)	
Weight (assembled)	Net:	7 oz (0.2 kg)
	Shipping:	1.3 lb (0.6 kg)
Ambient Operating Environment	32 to 104°F (0 to 40°C); 10% to 90% RH (non-condensing)	
Ambient Storage Temperature	–4 to 140°F (–20 to 60°C)	
Communication Ports	Ethernet Communication	RJ-45 (LIFE™ Services requires a network connection to the Internet)
	RJ-45 (RJ-45 to 2-position terminal-block adapter)	

WIRING

10/100 Mb/s Ethernet connector	Standard Category 5E Cable	328 ft. (100m)
RJ-45 - One-Wire Connector	Liebert® Integrated One-Wire Sensor Cable or 2m Cat 5E to Modular 1-Wire	65.6 ft. (20m)

VertivCo.com | **Vertiv Headquarters,** 1050 Dearborn Drive, Columbus, OH, 43085, USA

© 2017 Vertiv Co. All rights reserved. Vertiv and the Vertiv logo are trademarks or registered trademarks of Vertiv Co. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness herein, Vertiv Co. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications are subject to change without notice.

590-1307-501C/SL-52646_REV11_6-17