



Power Data Sheet Spec. No. 588705000 (Model PSS4850-23GV) Revision U, August 6, 2018

SYSTEM OVERVIEW



Preface:

This document provides power data and system application information for the following module mounting shelf used in a NetSure™ Power System.

Model Spec. No.		Description	
PSS4850-23GV	588705000	Module Mounting Shelf	

For rectifier and converter modules, refer to their separate instruction document as indicated in the following table.

Model	Spec. No.	Description	Document Number	
R48-3200	1R483200	Rectifier Module (PCU) (3200 watts)		
R48-3200e	1R483200E	DE High Efficiency Rectifier Module (PCU), (3200 watts) UM1R48		
R48-3500e	1R483500E	High Efficiency Rectifier Module (PCU), (3500 watts)		
C400/48-3500e	1C400483500E	High Efficiency Converter Module (3500 Watts)	UM1C400483500E	

Description:

A module mounting shelf and rectifier/converter modules, when used in a NetSure Power System equipped with a controller, comprise a -48V DC Power System designed to power a load while charging a positive grounded battery. This system is capable of operating in a battery-less installation or off battery for maintenance purposes. The system is designed for operation with the positive output grounded.


The NetSure Power System utilizing this equipment is an integrated power system containing rectifiers/converters, intelligent control, metering, and monitoring. A NetSure Power System, utilizing this equipment, typically consists of...

• Module Mounting Shelf

The system contains one or more module mounting shelves, which houses rectifier/converter modules. A shelf option is available which also houses the NCU Controller.

• Rectifier/Converter Modules

The system contains rectifier or converter modules, which provide load power, battery float current, and battery recharge current during normal operating conditions. Refer to the Rectifier Instructions (UM1R483500E) or Converter Instructions (UM1C400483500E) for more information.



Controller

The controller controls the operation of the rectifier and converter modules. The controller also provides power system control, metering, monitoring, and alarm functions. *Note:* This document does not describe the controller. Refer to the Power System SAG (System Application Guide) or separate Controller User Manual for controller information.

<u>Home</u>

General Specifications

See detailed specifications starting on page 36.

 Family:
 NetSure™

 Shelf Spec. No.:
 588705000

 Shelf Model:
 PSS4850-23GV

Shelf Input Ratings: List 1, 21, 31, 51, 61: 208 VAC, 240 VAC, 277 VAC, 50/60Hz, 1-Phase, 17.3A/15A.

<u>List 11, 22, 53, 63</u>: 208 VAC, 240 VAC, 50/60Hz, 1-Phase, 17.3A/15A. <u>List 3, 32, 52, 62</u>: 208 VAC, 240 VAC, 50/60Hz, 3-Phase, 29.3A/25.5A.

<u>List 33:</u> 277/480VAC, 50/60Hz, 3-Phase, 13.5A. <u>List 40, 41:</u> 260VDC to 400VDC, 14.6A. <u>List 42:</u> 260VDC to 400VDC, 44A.

Shelf Output Ratings: List 1, 3, 11, 21, 22, 31, 32, 33, 40, 41, 42, 51, 52, 53: -48VDC, 437A, 21000W

(maximum).

<u>List 61, 62, 63:</u> -48VDC, 364A, 17500W (maximum).

Rectifier Input Voltage: Nominal 208/240 or 277 volts AC, single phase, 50/60 Hz, with an operating

range of 176 to 305 volts. Acceptable input frequency range is 45 to 65 Hz.

Rectifier Output Voltage: -48 Volts DC, nominal.

Rectifier Output Capacity:

R48-3200 or R48-3200E: 55.2A @ -58.0VDC to 66.6A @ -48.0VDC, 3200 Watts (maximum). R48-3500E: 60.3A @ -58.0VDC to 72.9A @ -48.0VDC, 3500 Watts (maximum).

Converter Input Voltage: 260VDC to 400VDC.

Converter Output Voltage: -48 Volts DC, nominal.

Converter Output Capacity: 60.3A @ -58.0VDC to 72.9A @ -48.0VDC, 3500 Watts (maximum).

Agency Approval: UL 60950 Recognized; CAN/CSA 22.2, No. 60950-00

Framework Type: For Mounting in a 23 Inch Wide Relay Rack

Mounting Width: 23 Inch (Relay Rack Mounting)

Mounting Depth: <u>List 1, 3, 11, 21, 22, 31, 32, 33, 40, 41, 42</u>: 17.50 Inches

List 51, 52, 53, 61, 62, 63: 18.75 Inches

Mounting Height: 5.25 Inches (3U)

Front Projection: <u>List 1, 3, 11:</u> Adjustable (flush, 1", 2", 3", 4", 5", or 6").

<u>List 21, 22, 31, 32, 33, 40, 41, 42:</u> Fixed at 9". <u>List 51, 52, 53, 61, 62, 63:</u> Fixed at 6".

Access: Front and Rear for Installation and Maintenance,

Front for Operation

Control: Microprocessor

Color: Bright Zinc Plating, Body

Textured Gray, Faceplates

Environment: -40°C to +65°C (-40°F to +149°F)

TABLE OF CONTENTS


SYSTEM OVERVIEW	1
MAIN COMPONENTS ILLUSTRATIONS	5
LIST DESCRIPTIONS	6
List Numbers	
588705000 List 1: Rectifier Module Mounting Shelf, 208 VAC, 240 VAC, 277 VAC Input, Single-Phase, AC Input Terminal Blocks	
588705000 List 3: Rectifier Module Mounting Shelf, 208/240VAC Three-Phase Input, AC Input Terminal Blocks	
588705000 List 11: Rectifier Module Mounting Shelf, 208/240VAC Single-Phase Input, AC Input Line Cords	7
588705000 List 21: Rectifier Module Mounting Shelf, 208 VAC, 240 VAC, 277 VAC Input, No AC Input Terminal Blocks	7
588705000 List 22: Rectifier Module Mounting Shelf, 208/240VAC Single-Phase Input, AC Input Line Cords 588705000 List 31: Rectifier Module Mounting Shelf, 208 VAC, 240 VAC, 277 VAC Input, Single-Phase, AC Input Terminal Blocks	8
588705000 List 32: Rectifier Module Mounting Shelf, 208/240VAC Three-Phase Input, AC Input Terminal Blocks	
588705000 List 33: Rectifier Module Mounting Shelf, 277/480VAC Three-Phase Input, AC Input Terminal Blocks	
588705000 List 40: Converter Module Mounting Shelf, 400V DC Input, No DC Input Terminal Blocks	10
588705000 List 41: Converter Module Mounting Shelf, 400V DC Input, DC Input Terminal Blocks	10
588705000 List 42: Converter Module Mounting Shelf, 400V DC Input, DC Input Terminal Blocks	11
588705000 List 51: Expansion Rectifier Module Mounting Shelf, 208 VAC, 240 VAC, 277 VAC Input, Single-Phase, AC Input Terminal Blocks	11
588705000 List 52: Expansion Rectifier Module Mounting Shelf, 208/240VAC Three-Phase Input, AC Input Terminal Blocks	12
588705000 List 53: Expansion Rectifier Module Mounting Shelf, 208/240VAC Single-Phase Input, AC Input Line Cords	
588705000 List 61: Main Rectifier Module Mounting Shelf, 208 VAC, 240 VAC, 277 VAC Input, Single-Phase, AC Input Terminal Blocks	
588705000 List 62: Main Rectifier Module Mounting Shelf, 208/240VAC Three-Phase Input, AC Input Terminal Blocks	
588705000 List 63: Main Rectifier Module Mounting Shelf, 208/240VAC Single-Phase Input, AC Input Line Cords	14
ACCESSORY DESCRIPTIONS	15
Rectifiers	
High Efficiency Rectifier Module (PCU), P/N 1R483500E	
High Efficiency Rectifier Module (PCU), P/N 1R483200E	
Rectifier Module (PCU), P/N 1R483200	
Converters	
High Efficiency DC-DC Converter Module, P/N 1C400483500E	
NCU Controller (NetSure Control Unit), P/N 1M830DNA	
Module Mounting Position Blank Cover Panel	
Battery Charge Temperature Compensation Components	
Adding Additional Shelf in Field Output Busbar Kit	17
User Replaceable Cables	
User Replaceable Components	17
RECOMMENDED WIRE SIZES, BRANCH CIRCUIT PROTECTION, CRIMP LUGS, AND WIRING ILLUSTRATIONS	18
Shelf Frame Grounding Connection	
AC Input Connections	
List 1, 31, 51, and 61 Module Mounting Shelf (208 VAC, 240 VAC, 277 VAC Input, Single Phase)	
List 3, 32, 52, and 62 Module Mounting Shelf (208/240VAC Three Phase Input)	
List 33 Rectifier Shelf (277/480VAC Three Phase Input)	
List 11, 22, 53, and 63 Module Mounting Shelf (208/240VAC Single Phase Input)	
List 41 Module Mounting Shelf (400V DC Input)	
List 42 Module Mounting Shelf (400V DC Input)	
DC Output Connections	
External Alarms Connections	
SPECIFICATIONS	36
1. Module Mounting Shelf Specifications	36


	1.1 Output Ratings	36
	1.2 Input Ratings	36
	1.3 Environmental Ratings	36
	1.4 Compliance Information	37
	1.5 System Interface Board Ratings (List 61, 62, 63)	37
	1.1 Output Ratings	37
2.	Rectifier Specifications	37
3.	B. Converter Specifications	37
	HANICAL SPECIFICATIONS	
U	Medule Mounting Chalf (Liet 1.2 and 11)	
	Module Mounting Shelf (List 1, 3, and 11)	39
	Module Mounting Shelf (List 21 and List 40)	40
	Module Mounting Shelf (61, 62, and 63)	41
	Module Mounting Shelf (List 51, 52, and 53)	42
RELA	ATED DOCUMENTATION	
RFVI9	SION RECORD	66

Revision U, August 6, 2018

MAIN COMPONENTS ILLUSTRATIONS







LIST DESCRIPTIONS

<u>Home</u>


List Numbers

588705000 List 1:

Rectifier Module Mounting Shelf, 208 VAC, 240 VAC, 277 VAC Input, Single-Phase, AC Input Terminal Blocks

Features

- Provides one (1) Model PSS4850-23GV, Spec. No. 588705000 Module Mounting Shelf (-48V, 437A/21000W).
- This module mounting shelf holds up to six (6) rectifier modules.
- This module mounting shelf is equipped with individual rectifier module single-phase AC input feeds (one AC input branch circuit per rectifier module, six AC input branch circuits per module mounting shelf).
- Terminal blocks provided for AC input connections.



Restrictions

Relay rack mounting angle provides maximum six (6) inch front projection.

Ordering Notes

- 1) Order rectifier modules as required per P/N 1R483200, P/N 1R483200E, or P/N 1R483500E.
- Order a module mounting position blank cover panel, P/N 21140440, for each empty module mounting position in the system, as desired.
- 3) Refer also to "ACCESSORY DESCRIPTIONS".

588705000 List 3:

Rectifier Module Mounting Shelf, 208/240VAC Three-Phase Input, AC Input Terminal Blocks

Features

- Provides one (1) Model PSS4850-23GV, Spec. No. 588705000 Module Mounting Shelf (-48V, 437A/21000W).
- This module mounting shelf holds up to six (6) rectifier modules.
- This module mounting shelf is equipped with two (2) threephase AC input circuits. Each input circuit powers three (3) single-phase rectifier modules.
- Terminal blocks provided for AC input connections.

Restrictions

To maintain phase balance, rectifier modules should be installed in groups of three (all three on left and/or all three on right). Relay rack mounting angle provides maximum six (6) inch front projection.

- Order rectifier modules in groups of three per P/N <u>1R483200</u>, P/N <u>1R483200E</u>, or P/N <u>1R483500E</u>.
- 2) Order a module mounting position blank cover panel, P/N 21140440, for each empty module mounting position in the system, as desired.
- 3) Refer also to "ACCESSORY DESCRIPTIONS".


588705000 List 11:

Features

 Provides one (1) Model PSS4850-23GV, Spec. No. 588705000 Module Mounting Shelf (-48V, 437A/21000W).

Rectifier Module Mounting Shelf, 208/240VAC Single-Phase Input, AC Input Line Cords

- This module mounting shelf holds up to six (6) rectifier modules.
- This module mounting shelf is equipped with individual rectifier module single-phase AC input feeds (one AC input branch circuit per rectifier module, six AC input branch circuits per module mounting shelf).
- Factory wired AC input line cords equipped with NEMA L6-30P twist-lock plugs provided. (Six per shelf, each 7.5' long, 12/3 AWG.)



Restrictions

Line cord option can only be used up to 40°C ambient.

Relay rack mounting angle provides maximum six (6) inch front projection.

Ordering Notes

- Order rectifier modules as required per P/N 1R483200, P/N 1R483200E, or P/N 1R483500E.
- Order a module mounting position blank cover panel, P/N 21140440, for each empty module mounting position in the system, as desired.
- 3) Refer also to "ACCESSORY DESCRIPTIONS".

588705000 List 21:

Rectifier Module Mounting Shelf, 208 VAC, 240 VAC, 277 VAC Input, No AC Input Terminal Blocks


Features

- Provides one (1) Model PSS4850-23GV, Spec. No. 588705000 Module Mounting Shelf (-48V, 437A/21000W).
- This module mounting shelf holds up to six (6) rectifier modules.
- NO terminal blocks provided for AC input connections.

Restrictions

Module mounting shelf MUST be factory wired into power system. Relay rack mounting angles fixed at 9" front projection.

- Order rectifier modules as required per P/N <u>1R483200</u>, P/N <u>1R483200E</u>, or P/N <u>1R483500E</u>.
- 2) Order a module mounting position blank cover panel, P/N 21140440, for each empty module mounting position in the system, as desired.
- 3) Refer also to "ACCESSORY DESCRIPTIONS".




588705000 List 22:

Rectifier Module Mounting Shelf, 208/240VAC Single-Phase Input, AC Input Line Cords

<u>Home</u>

Features

- Provides one (1) Model PSS4850-23GV, Spec. No. 588705000 Module Mounting Shelf (-48V, 437A/21000W).
- This module mounting shelf holds up to six (6) rectifier modules.
- This module mounting shelf is equipped with individual rectifier module single-phase AC input feeds (one AC input branch circuit per rectifier module, six AC input branch circuits per module mounting shelf).
- Factory wired AC input line cords equipped with NEMA L6-30P twist-lock plugs provided. (Six per shelf, each 7.5' long, 12/3 AWG.)



Restrictions

Line cord option can only be used up to 40°C ambient.

Relay rack mounting angles fixed at 9" front projection.

Ordering Notes

- 1) Order rectifier modules as required per P/N 1R483200, P/N 1R483200E, or P/N 1R483500E.
- Order a module mounting position blank cover panel, P/N 21140440, for each empty module mounting position in the system, as desired.
- 3) Refer also to "ACCESSORY DESCRIPTIONS".

588705000 List 31:

Rectifier Module Mounting Shelf, 208 VAC, 240 VAC, 277 VAC Input, Single-Phase, AC Input Terminal Blocks

Features

- Provides one (1) Model PSS4850-23GV, Spec. No. 588705000 Module Mounting Shelf (-48V, 437A/21000W).
- This module mounting shelf holds up to six (6) rectifier modules.
- This module mounting shelf is equipped with individual rectifier module single-phase AC input feeds (one AC input branch circuit per rectifier module, six AC input branch circuits per module mounting shelf).
- Terminal blocks provided for AC input connections.

Restrictions

Relay rack mounting angles fixed at 9" front projection.

- Order rectifier modules as required per P/N 1R483200, P/N 1R483200E, or P/N 1R483500E.
- 2) Order a module mounting position blank cover panel, P/N 21140440, for each empty module mounting position in the system, as desired.
- 3) Refer also to "ACCESSORY DESCRIPTIONS".

588705000 List 32:

Features

 Provides one (1) Model PSS4850-23GV, Spec. No. 588705000 Module Mounting Shelf (-48V, 437A/21000W).

Rectifier Module Mounting Shelf, 208/240VAC Three-Phase Input, AC Input Terminal Blocks

- This module mounting shelf holds up to six (6) rectifier modules.
- This module mounting shelf is equipped with two (2) threephase AC input circuits. Each input circuit powers three (3) single-phase rectifier modules.
- Terminal blocks provided for AC input connections.



To maintain phase balance, rectifier modules should be installed in groups of three (all three on left and/or all three on right). Relay rack mounting angles fixed at 9" front projection.

Ordering Notes

- Order rectifier modules in groups of three per P/N <u>1R483200</u>, P/N <u>1R483200E</u>, or P/N <u>1R483500E</u>.
- Order a module mounting position blank cover panel, P/N 21140440, for each empty module mounting position in the system, as desired.
- 3) Refer also to "ACCESSORY DESCRIPTIONS".

588705000 List 33:

Rectifier Module Mounting Shelf, 277/480VAC Three-Phase Input, AC Input Terminal Blocks


Features

- Provides one (1) Model PSS4850-23GV, Spec. No. 588705000 Module Mounting Shelf (-48V, 437A/21000W).
- This module mounting shelf holds up to six (6) rectifier modules.
- This module mounting shelf is equipped with two (2) threephase AC input circuits. Each input circuit powers three (3) single-phase rectifier modules.
- Terminal blocks provided for AC input connections.

Restrictions

To maintain phase balance, rectifier modules should be installed in groups of three (all three on left and/or all three on right). Relay rack mounting angles fixed at 9" front projection.

- 1) Order rectifier module P/N 1R483500E only.
- 2) Order a module mounting position blank cover panel, P/N 21140440, for each empty module mounting position in the system, as desired.
- 3) Refer also to "ACCESSORY DESCRIPTIONS".



588705000 List 40:

Converter Module Mounting Shelf, 400V DC Input, No DC Input Terminal Blocks

Features


- Provides one (1) Model PSS4850-23GV, Spec. No. 588705000 Module Mounting Shelf (-48V, 437A/21000W).
- This module mounting shelf holds up to six (6) converter modules.
- ♦ NO terminal blocks provided for DC input connections.

Restrictions

Module mounting shelf MUST be factory wired into power system. Relay rack mounting angles fixed at 9" front projection.

Ordering Notes

- 1) Order converter modules as required per P/N <u>1C400483500E</u>.
- Order a module mounting position blank cover panel, P/N 21140440, for each empty module mounting position in the system, as desired.
- 3) Refer also to "ACCESSORY DESCRIPTIONS".



Converter Module Mounting Shelf, 400V DC Input, DC Input Terminal Blocks

Features


- Provides one (1) Model PSS4850-23GV, Spec. No. 588705000 Module Mounting Shelf (-48V, 437A/21000W).
- This module mounting shelf holds up to six (6) converter modules.
- This module mounting shelf is equipped with individual converter module DC input feeds (one DC input branch circuit per converter module, six DC input branch circuits per module mounting shelf).
- Terminal blocks provided for DC input connections.


Restrictions

DC inputs MUST be wired directly to the shelf.

Relay rack mounting angles fixed at 9" front projection.

- 1) Order converter modules as required per P/N 1C400483500E.
- 2) Order a module mounting position blank cover panel, P/N 21140440, for each empty module mounting position in the system, as desired.
- 3) Refer also to "ACCESSORY DESCRIPTIONS".





588705000 List 42:

Converter Module Mounting Shelf, 400V DC Input, DC Input Terminal Blocks

<u>Home</u>

Features

- Provides one (1) Model PSS4850-23GV, Spec. No. 588705000 Module Mounting Shelf (-48V, 437A/21000W).
- This module mounting shelf holds up to six (6) converter modules.
- This module mounting shelf is equipped with two (2) DC input circuits. Each input circuit powers three (3) converter modules.
- ♦ Terminal blocks provided for DC input connections.

Restrictions

DC inputs MUST be wired directly to the shelf.

Relay rack mounting angles fixed at 9" front projection.

Ordering Notes

- Order converter modules as required per P/N <u>1C400483500E</u>.
- Order a module mounting position blank cover panel, P/N 21140440, for each empty module mounting position in the system, as desired.
- 3) Refer also to "ACCESSORY DESCRIPTIONS".



Expansion Rectifier Module Mounting Shelf, 208 VAC, 240 VAC, 277 VAC Input, Single-Phase, AC Input Terminal Blocks


Features

- Provides one (1) Model PSS4850-23GV, Spec. No. 588705000 Module Mounting Shelf (-48V, 437A/21000W).
- This module mounting shelf holds up to six (6) rectifier modules.
- This module mounting shelf is equipped with individual rectifier module single-phase AC input feeds (one AC input branch circuit per rectifier module, six AC input branch circuits per module mounting shelf).
- ♦ Terminal blocks provided for AC input connections.

Restrictions

Relay rack mounting angles fixed at 6" front projection.

- 1) Order rectifier modules as required per P/N 1R483200, P/N 1R483200E, or P/N 1R483500E.
- 2) Order a module mounting position blank cover panel, P/N 21140440, for each empty module mounting position in the system, as desired.
- 3) Refer also to "ACCESSORY DESCRIPTIONS".





588705000 List 52:

Expansion Rectifier Module Mounting Shelf, 208/240VAC Three-Phase Input, AC Input Terminal Blocks

<u>Home</u>

Features

- Provides one (1) Model PSS4850-23GV, Spec. No. 588705000 Module Mounting Shelf (-48V, 437A/21000W).
- This module mounting shelf holds up to six (6) rectifier modules.
- This module mounting shelf is equipped with two (2) threephase AC input circuits. Each input circuit powers three (3) single-phase rectifier modules.
- ♦ Terminal blocks provided for AC input connections.



Restrictions

To maintain phase balance, rectifier modules should be installed in groups of three (all three on left and/or all three on right). Relay rack mounting angles fixed at 6" front projection.

Ordering Notes


- Order rectifier modules in groups of three per P/N <u>1R483200</u>, P/N <u>1R483200E</u>, or P/N <u>1R483500E</u>.
- Order a module mounting position blank cover panel, P/N 21140440, for each empty module mounting position in the system, as desired.
- 3) Refer also to "ACCESSORY DESCRIPTIONS".

588705000 List 53:

Expansion Rectifier Module Mounting Shelf, 208/240VAC Single-Phase Input, AC Input Line Cords

Features

- Provides one (1) Model PSS4850-23GV, Spec. No. 588705000 Module Mounting Shelf (-48V, 437A/21000W).
- This module mounting shelf holds up to six (6) rectifier modules.
- This module mounting shelf is equipped with individual rectifier module single-phase AC input feeds (one AC input branch circuit per rectifier module, six AC input branch circuits per module mounting shelf).
- Factory wired AC input line cords equipped with NEMA L6-30P twist-lock plugs provided. (Six per shelf, each 7.5' long, 12/3 AWG.)



Restrictions

Line cord option can only be used up to 40°C ambient.

Relay rack mounting angles fixed at 6" front projection.

- 1) Order rectifier modules as required per P/N 1R483200, P/N 1R483200E, or P/N 1R483500E.
- 2) Order a module mounting position blank cover panel, P/N 21140440, for each empty module mounting position in the system, as desired.
- Refer also to "<u>ACCESSORY DESCRIPTIONS</u>".

588705000 List 61:

Home Main Rectifier Module Mounting Shelf, 208 VAC, 240 VAC, 277 VAC Input, Single-Phase, AC Input Terminal Blocks

Features

- Provides one (1) Model PSS4850-23GV, Spec. No. 588705000 Module Mounting Shelf (-48V, 364A/17500W).
- This module mounting shelf holds up to five (5) rectifier modules and one (1) NCU Controller.
- This module mounting shelf is equipped with individual rectifier module single-phase AC input feeds (one AC input branch circuit per rectifier module, five AC input branch circuits per module mounting shelf).
- Terminal blocks provided for AC input connections.
- Also provided is the system interface board which provides two (2) external battery fuse alarm inputs, four (4) external load fuse alarm inputs, one (1) load shunt input, one (1) battery shunt input, one (1) LVD driver output, one (1) LVD sense input, and RS-485 port.
- Also provided is the IB2 controller interface board which provides eight (8) programmable form-C relay outputs, eight (8) programmable binary inputs, and two (2) temperature inputs.



Relay rack mounting angles fixed at 6" front projection.

Ordering Notes

- Order rectifier modules as required per P/N <u>1R483200</u>, P/N <u>1R483200E</u>, or P/N <u>1R483500E</u>.
- Order a module mounting position blank cover panel, P/N 21140440, for each empty module mounting position in the system, as desired.
- Order one (1) NCU controller, P/N 1M830DNA.
- Refer also to "ACCESSORY DESCRIPTIONS".

588705000 List 62:

Main Rectifier Module Mounting Shelf, 208/240VAC Three-Phase Input, AC Input Terminal Blocks


Features


- Provides one (1) Model PSS4850-23GV, Spec. No. 588705000 Module Mounting Shelf (-48V, 364A/17500W).
- This module mounting shelf holds up to five (5) rectifier modules and one (1) NCU Controller.
- This module mounting shelf is equipped with two (2) threephase AC input circuits. One input powers three (3) singlephase rectifiers (left side) and one input powers two (2) single-phase rectifiers (right side).
- Terminal blocks provided for AC input connections.
- Also provided is the system interface board which provides two (2) external battery fuse alarm inputs, four (4) external load fuse alarm inputs, one (1) load shunt input, one (1) battery shunt input, one (1) LVD driver output, one (1) LVD sense input, and RS-485 port.
- Also provided is the IB2 controller interface board which provides eight (8) programmable form-C relay outputs, eight (8) programmable binary inputs, and two (2) temperature inputs.

Restrictions

Relay rack mounting angles fixed at 6" front projection.

- Order rectifier modules per P/N 1R483200, P/N 1R483200E, or P/N 1R483500E.
- Order a module mounting position blank cover panel, P/N 21140440, for each empty module mounting position in the system, as desired.





- 3) Order one (1) NCU controller, P/N 1M830DNA.
- 4) Refer also to "ACCESSORY DESCRIPTIONS".


<u>Home</u>

588705000 List 63:

Main Rectifier Module Mounting Shelf, 208/240VAC Single-Phase Input, AC Input Line Cords

Features

- Provides one (1) Model PSS4850-23GV, Spec. No. 588705000 Module Mounting Shelf (-48V, 364A/17500W).
- This module mounting shelf holds up to five (5) rectifier modules and one (1) NCU Controller.
- This module mounting shelf is equipped with individual rectifier module single-phase AC input feeds (one AC input branch circuit per rectifier module, five AC input branch circuits per module mounting shelf).
- Factory wired AC input line cords equipped with NEMA L6-30P twist-lock plugs provided. (Five per shelf, each 7.5' long, 12/3 AWG.)




♦ Also provided is the IB2 controller interface board which provides eight (8) programmable form-C relay outputs, eight (8) programmable binary inputs, and two (2) temperature inputs.

Restrictions

Line cord option can only be used up to 40°C ambient.

Relay rack mounting angles fixed at 6" front projection.

- 1) Order rectifier modules as required per P/N 1R483200, P/N 1R483200E, or P/N 1R483500E.
- 2) Order a module mounting position blank cover panel, P/N 21140440, for each empty module mounting position in the system, as desired.
- 3) Order one (1) NCU controller, P/N 1M830DNA.
- 4) Refer also to "ACCESSORY DESCRIPTIONS".



ACCESSORY DESCRIPTIONS

Rectifiers

High Efficiency Rectifier Module (PCU), P/N 1R483500E

Features

- Provides one (1) Model R48-3500e, Spec. No. 1R483500E, 3500 watt / -48 volt rectifier module.
- ♦ Refer to the Rectifier Instructions (UM1R483500E) for more information.

Restrictions

Refer to the power system's SAG (System Application Guide) for any compatibility issues in using this rectifier in power systems manufactured before this rectifier was available.

For use in List 1, 3, 11, 21, 22, 31, 32, 33, 51, 52, 53, 61, 62, and 63 shelves.

Ordering Notes

Order as required.



High Efficiency Rectifier Module (PCU), P/N 1R483200E

Features

- Provides one (1) Model R48-3200e, Spec. No. 1R483200E, 3200 watt / -48 volt rectifier module.
- Refer to the Rectifier Instructions (UM1R483500E) for more information.

Restrictions

For use in List 1, 3, 11, 21, 22, 31, 32, 51, 52, 53, 61, 62, and 63 shelves.

Ordering Notes

Order as required.

Rectifier Module (PCU), P/N 1R483200

Features

- Provides one (1) Model R48-3200, Spec. No. 1R483200, 3200 watt / -48 volt rectifier module.
- Refer to the Rectifier Instructions (UM1R483500E) for more information.

Restrictions

For use in List 1, 3, 11, 21, 22, 31, 32, 51, 52, 53, 61, 62, and 63 shelves.

Ordering Notes

1) Order as required.



Converters

High Efficiency DC-DC Converter Module, P/N 1C400483500E

Features

- Provides one (1) Model C400/48-3500e, Spec. No. 1C400483500E, 3500 watt / 400 to -48 volt DC-DC converter module.
- ♦ Refer to the Converter Instructions (UM1C400483500E) for more information.

Restrictions

For use in List 40, 41, and 42 shelves.

Ordering Notes

Order as required.

NCU Controller (NetSure Control Unit), P/N 1M830DNA

Features

- Provides one (1) Model M830DNA, Spec. No. 1M830DNA system controller.
- Factory programmed with the configuration file required for the system configuration ordered.

Note: For custom NCU configurations, contact Vertiv.

Restrictions

For use in List 61, 62, and 63 only.

Ordering Notes

- 1) Order one (1) NCU Controller (P/N 1M830DNA) per power system (to be installed in a main module mounting shelf List 61, 62, or 63).
- Oder additional NCU accessories per the power system's SAG (System Application Guide).

Module Mounting Position Blank Cover Panel

Features

Covers one (1) unused module mounting position.

Ordering Notes

1) Order a module mounting position blank cover panel, P/N 21140440, for each empty module mounting position in the system, as desired.


Battery Charge Temperature Compensation Components


Ordering Notes

1) Refer to the power system's SAG (System Application Guide) for battery charge temperature compensation components.



Home





Spec. No. 588705000 (Model PSS4850-23GV) Revision U, August 6, 2018

Adding Additional Shelf in Field Output Busbar Kit



Features


Kit to tie the DC output busbars in a field installed module mounting shelf to the DC busbars in a Spec. No. 582126000 or 582127000 NetSure Power System.

Restrictions

Not for use with List 51, 52, 53, 61, 62, or 63.

Ordering Notes

Order kit P/N 529139 for each module mounting shelf to be added in the field.



and Hardware

User Replaceable Cables

Ordering Notes

Refer to the power system's SAG (System Application Guide) for part numbers.

User Replaceable Components

Ordering Notes

Rectifier Module Fan: P/N 32010086 for 1R483200 rectifier module.

P/N 32010109 for 1R483200E and 1R483500E rectifier module.

Converter Module Fan: P/N 32010109 for 1C400483500E converter module.

RECOMMENDED WIRE SIZES, BRANCH CIRCUIT PROTECTION, CRIMP LUGS, AND WIRING ILLUSTRATIONS

Shelf Frame Grounding Connection

Located at the rear of the shelf are terminals for a grounding connection. See Table 1 for recommended frame grounding wire size and Figure 1, Figure 2, Figure 3, Figure 5, Figure 8, or Figure 9 for terminal location.

FRAME GROUND (FR GND) 1				
Terminals	Recm Wire Size			
Two 10-32 X 3/4" Studs and Hardware	10 AWG			

- This terminal must be connected to earth ground, not power system neutral. Equipment grounding conductor size based on recommendations of the NEC Table 250-122 for copper wire. If aluminum or copper clad aluminum grounding conductor is used, refer to Table 250-122 for increased conductor size. For operation in countries where the NEC is not recognized, follow applicable codes.
- For shelf grounding requirements, refer to the current edition of the American National Standards Institute (ANSI) approved National Fire Protection Association's (NFPA) National Electrical Code (NEC), applicable local codes, and your specific site requirements.

Table 1 Recommended Frame Grounding Wire Size

AC Input Connections

List 1, 31, 51, and 61 Module Mounting Shelf (208 VAC, 240 VAC, 277 VAC Input, Single Phase)

Refer to Table 2 for recommended wire size and Figure 1 or Figure 2 for terminal location.

Connec	LIST 1, 31, 51, AND 61 AC INPUT (TB1 and TB2) Connection Points for Individual Rectifier Module AC Input Branch Circuits are Provided (One AC Input Branch Circuit per Rectifier Module, Five [List 61] or Six [List 1, 31, 51] AC Input Branch Circuits per Shelf)						
Operating	Recm		TB1 and TI	32 Terminals			
Ambient Temperature ¹	Branch Circuit Protection ^{2, 3}	Recm 90°C Wire Size ¹	Capacity	Туре			
30°C		10 AWG	List 1, 31:	Screw Compression Tubular Contact			
40°C	25 Amperes		10 to 24 AWG List 51, 61:				
65°C			6 to 14 AWG				

- Wire sizes based on recommendations of the American National Standards Institute (ANSI) approved National Fire Protection Association's (NFPA) National Electrical Code (NEC). Table 310.15 (B) (16) for copper wire at 90°C conductor temperature. For operation in countries where the NEC is not recognized, follow applicable codes.
- The AC input branch circuit protective device should be of the time-delay or high inrush type.
- Recommendations based on Nominal Line Full Load Input Current of 18 Amperes.

Table 2

Recommended AC Input Branch Circuit Protection and Wire Size - List 1, 31, 51, and 61




Figure 1
List 1 and 31 AC Input and Frame Ground Connections (Single-Phase Input) (Terminal Blocks)




Figure 2
List 51 and 61 AC Input and Frame Ground Connections (Single-Phase Input) (Terminal Blocks)

Revision U, August 6, 2018

Home

List 3, 32, 52, and 62 Module Mounting Shelf (208/240VAC Three Phase Input)

Refer to Table 3 for recommended wire size and Figure 3 or Figure 5 for terminal location.

LIST 3, 32, 52, AND 62 AC INPUT (TB1 and TB2) Connection Points for Two 3-Phase AC Input Feeds are Provided per Shelf						
Operating	Operating Recm		TB1 and TB2 Terminals			
Ambient Temperature ¹	Branch Circuit Protection ^{2, 3}	Recm 90°C Wire Size ¹	Capacity	Туре		
30°C	40 Amperes, 3-Pole	8 AWG	6 to 14 AWG	Screw Compression Tubular Contact		
40°C						
65°C						

Wire sizes based on recommendations of the American National Standards Institute (ANSI) approved National Fire Protection Association's (NFPA) National Electrical Code (NEC). Table 310.15 (B) (16) for copper wire at 90°C conductor temperature. For operation in countries where the NEC is not recognized, follow applicable codes.

Table 3

Recommended AC Input Branch Circuit Protection and Wire Size - List 3, 32, 52, and 62

The AC input branch circuit protective device should be of the time-delay or high inrush type.

Recommendations based on Nominal Line Full Load Input Current of 29.3 Amperes.




Figure 3
List 3 and 32 AC Input and Frame Ground Connections (Three-Phase Input) (Terminal Blocks)

Revision U, August 6, 2018

List 33 Rectifier Shelf (277/480VAC Three Phase Input)

<u>Home</u>

Refer to Table 4 for recommended wire size and Figure 4 for terminal location.

LIST 33 AC Input (TB1 and TB2)						
Operating	Operating Recm		TB1 and TB2 Terminals			
Operating Ambient Temperature ¹	bient	Recommended 90°C Wire Size ¹	Capacity	Туре		
30°C		12 AWG	8 to 24 AWG	Screw Compression Tubular Contact		
40°C	20A					
65°C						

Wire sizes based on recommendations of the American National Standards Institute (ANSI) approved National Fire Protection Association's (NFPA) National Electrical Code (NEC). Table 310.15 (B) (16) for copper wire at 90°C conductor temperature. For operation in countries where the NEC is not recognized, follow applicable codes.

Table 4

Recommended AC Input Branch Circuit Protection and Wire Size - List 33

The AC input branch circuit protective device should be of the time-delay or high inrush type.

Recommendations based on Nominal Line Full Load Input Current of 13.5 Amperes.





Figure 4
List 33 AC Input and Frame Ground Connections (Three-Phase Input) (Terminal Blocks)

<u>Home</u>



CONNECTIONS WITHIN THE SHELF

Mounting	TE	31, Term	ninal	TB	2, Termi	inal
Position	1 (ØA)	2 (ØB)	3 (ØC)	1 (ØA)	2 (ØB)	3 (ØC)
Rect 1	L1	L2				
Rect 2	L1		L2			
Rect 3		L1	L2			
Rect 4				L1	L2	
Rect 5				L1		L2
Rect 6					L1	L2

AC IN: 208-240VAC, 50/60Hz, THREE PHASE Wire Size Capacity: 6-14 AWG.

Recommended Torque: 6 AWG, 45 in-lbs. 8-14 AWG, 35 in-lbs.

List 52 only

Figure 5

List 52 and 62 AC Input and Frame Ground Connections (Three-Phase Input) (Terminal Blocks)

List 11, 22, 53, and 63 Module Mounting Shelf (208/240VAC Single Phase Input)



Refer to Table 5 for recommended wire size and Figure 6 or Figure 7 for terminal location.

Line Cord	LIST 11, 22, 53, AND 63 AC INPUT (Line Cords) Line Cords for Individual Rectifier Module AC Input Branch Circuits are Factory Connected (One AC Input Branch Circuit per Rectifier Module, Five [List 63] or Six [List 11, 22, 53] AC Input Branch Circuits per Shelf)				
Operating Ambient Temperature	Recm Branch Circuit Protection ^{1, 2}				
30°C	25 Amparas				
40°C ³	25 Amperes				

- The AC input branch circuit protective device should be of the time-delay or high inrush type.
- Recommendations based on Nominal Line Full Load Input Current of 18 Amperes.
- ³ Line cord option can only be used up to 40°C ambient.

Table 5 Recommended AC Input Branch Circuit Protection and Wire Size - List 11, 22, 53, and 63








Figure 6
List 11 and 22 AC Input Connections (Single-Phase Input) (Line Cords)





List 53 and 63 AC Input Connections (Single-Phase Input) (Line Cords)

Revision U, August 6, 2018

Home

List 41 Module Mounting Shelf (400V DC Input)


Refer to Table 6 for recommended wire size and Figure 8 for terminal location.

LIST 41 DC INPUT (TB1 and TB2) Connection Points for Individual Rectifier Module DC Input Branch Circuits are Provided (One DC Input Branch Circuit per Rectifier Module, Six DC Input Branch Circuits per Shelf)						
Recm TB1 and TB2 Terminals						
Operating Ambient Temperature ¹		Recm 90°C Wire Size ^{1,4}	Capacity	Туре		
45°C		12 AWG	10 to 20 AWG	Screw Compression Tubular Contact		
50°C	20 Amperes					
65°C²						

- Wire sizes based on recommendations of the American National Standards Institute (ANSI) approved National Fire Protection Association's (NFPA) National Electrical Code (NEC). Table 310.15 (B) (16) for copper wire at 90°C conductor temperature. For operation in countries where the NEC is not recognized, follow applicable codes.
- Converters de-rate to 2700W at an ambient of 65°C.
- Recommendations based on Full Load Input Current of 14.6 Amperes.
- Maximum loop length is 100 meters (328 feet). Loop length is the sum of the lengths of the positive and negative leads.

Table 6 Recommended DC Input Branch Circuit Protection and Wire Size - List 41

Spec. No. 588705000 (Model PSS4850-23GV) **Home** Rear View Holes for 3/4" Conduit Fitting (Input) (3)



Holes for 3/4" Conduit Fitting (Input)

Conv. Conv. Conv. Conv. Conv.

Converter Module Mounting Slots

(front view)

Recommended torque: 23 in-lbs.

INDIVIDUAL 400VDC CONVERTER FEEDS 1 FEED PER CONVERTER

Figure 8 List 41 DC Input and Frame Ground Connections (Terminal Blocks)

Spec. No. 588705000 (Model PSS4850-23GV)

Power Data Sheet

Revision U, August 6, 2018

<u>Home</u>

List 42 Module Mounting Shelf (400V DC Input)

Refer to Table 7 for recommended wire size and Figure 9 for terminal location.

LIST 42 DC INPUT (TB1 and TB2) Connection Points for Two DC Input Feeds are Provided per Shelf					
Operating	Recm		TB1 and TB2 Terminals		
Ambient Temperature ¹	Branch Circuit Protection ^{3, 4}	Recm 90°C Wire Size ^{1,5}	Capacity	Туре	
45°C		6 AWG	6 to 14 AWG	Screw Compression Tubular Contact	
50°C	60 Amperes				
65°C²	65°C²				

- Wire sizes based on recommendations of the American National Standards Institute (ANSI) approved National Fire Protection Association's (NFPA) National Electrical Code (NEC). Table 310.15 (B) (16) for copper wire at 90°C conductor temperature. For operation in countries where the NEC is not recognized, follow applicable codes.
- ² Converters de-rate to 2700W at an ambient of 65°C.
- Recommendations based on Full Load Input Current of 44 Amperes.
- ⁴ Maximum overcurrent protective device is 70A at 40°C.
- Maximum loop length is 100 meters (328 feet). Loop length is the sum of the lengths of the positive and negative

Table 7
Recommended DC Input Branch Circuit Protection and Wire Size - List 42

Home Holes for 3/4" Conduit Fitting (Input) Conv. Conv. Conv. Conv. Conv. 3 Rear View Holes for 3/4" Converter Module Mounting Slots Conduit Fitting (front view) (Input) \bigoplus \bigcirc ED ED (B) SD ED ED 0 \bigcirc \bigcirc 0 Rear View Wire Size Capacity: 6-14 AWG. Recommended Torque: 18 in-lbs. TB2 0 0 ТВІ 400VDC IN 400VDC IN **(** Feed 2 Feed 1 0 (Converter **(1) (** $\langle Q \rangle$ (Converter Modules 0 Modules 4-6) 0 0 1-3) 0 0 0 FRAME GROUND CONNECTION FRAME GROUND CONNECTION ONE 10-32 X 3/4" STUD ONE 10-32 X 3/4" STUD AND HARDWARE. AND HARDWARE. Recommended torque: 23 in-lbs.

CONVERTER 400VDC INPUT FEEDS 1 FEED PER 3 CONVERTERS

Recommended torque: 23 in-lbs.

Figure 9
List 42 DC Input and Frame Ground Connections (Terminal Blocks)

Power Data Sheet Spec. No. 588705000 (Model PSS4850-23GV) PD588705000

Revision U, August 6, 2018

DC Output Connections



Shelf DC output is connected via busbars to a NetSure Power System. No wire size or lug recommendations provided here. Refer to Figure 10 and Figure 11.

External Alarms Connections

Shelf external alarms are provided via the Controller. Refer to the associated power system documentation for external alarm information. No wire size recommendations provided here. Refer to Figure 10 and Figure 11 for controller interconnections.





Figure 10
DC Output and Alarm/Control Connections
(List 1, 3, 11, 21, 22, 31, 32, 40, 41, 42)

<u>Home</u>






Figure 11
DC Output and Alarm/Control Connections
(List 51, 52, 53, 61, 62, 63)

SPECIFICATIONS



Note: Refer to the separate System Application Guide (SAG) of the associated Power System for the following:

- MCA Controller specifications and factory default settings.
- NCU Controller specifications and factory default settings.
- All external alarms.
- All external controls.
- Local status and alarm indicators other than those provided on the rectifier and converter modules.
- MODULE MOUNTING SHELF SPECIFICATIONS
 - 1.1 Output Ratings
 - 1.1.1 See page 2.
 - 1.2 Input Ratings
 - 1.2.1 See page 2.
 - 1.3 Environmental Ratings
 - 1.3.1 Operating Ambient Temperature Range: -40°C to +65°C (-40°F to +149°F).
 - 1.3.2 Storage Ambient Temperature Range: -40°C to +85°C (-40°F to +185°F).
 - 1.3.3 **Humidity:** Capable of operating in an ambient relative humidity range of 0% to 95%, non-condensing.
 - 1.3.4 **Altitude:** Capable of operating in an altitude range of -200 feet to 10,000 feet. The maximum operating ambient temperature should be de-rated by 3°C per 1000 feet above 5000 feet.
 - 1.3.5 Ventilation Requirements:
 - (A) **Ventilation:** A module mounting shelf must be mounted so ventilating openings are not blocked and temperature of the air entering the cabinet does not exceed the Operating Ambient Temperature Range stated above. The distance from the rear of a module mounting shelf to a wall or other solid structure must not be less than two (2) inches. This will assure proper airflow through the rectifier modules. (See also Paragraph 1.3.6.)
 - (B) **Stacking Considerations:** This system is designed for front to back ventilation to facilitate stacking of module mounting shelves, one above the other, in a relay rack. There is no spacing requirement between stacked module mounting shelves of a single system.
 - 1.3.6 **Mounting:** The module mounting shelves are designed for mounting in a 23 inch wide relay rack with 1 inch or 1-3/4 inch multiple drilling. For Lists 1, 3, and 11; mounting angles can be positioned from flush-front mounting to 6-inch front projection mounting, in 1-inch increments. For Lists 21, 22, 31, 32, 33, 40, 41, and 42; mounting angles are positioned for a fixed 9-inch front projection mounting. For Lists 51, 52, 53, 61, 62, and 63; mounting angles are positioned for a fixed 6-inch front projection mounting. Refer to Overall Dimensions starting on page 38 for dimensional illustrations.
 - This product is intended only for installation in a restricted access location on or above a non-combustible surface.
 - This product must be located in a controlled environment with access to crafts persons only.
 - This product is intended for installation in network telecommunication facilities (CO, vault, hut, or other environmentally controlled electronic equipment enclosure).
 - This product is intended to be connected to the common bonding network in a network telecommunication facility (CO, vault, hut, or other environmentally controlled electronic equipment enclosure).
 - The DC return connection to this system can remain isolated from system frame and chassis (DC-I).
 - This system is suitable for installation as part of the Common Bonding Network (CBN).
 - Rectifier and module mounting shelf ventilating openings must not be blocked and temperature of air entering rectifiers must not exceed the rated operating ambient temperature range.
 - Clearance requirements are:
 - a) Recommended minimum aisle space clearance for the front of the unit is 2' 6".
 - b) See Paragraph 1.3.5 for minimum rear spacing requirements.

Note: Minimum rear spacing specified for ventilation may not permit installation and maintenance of the system.

No. 588705000 (Model PSS4850-23GV) Revision U, August 6, 2018

<u>Home</u>

Recommended minimum aisle space clearance for the rear of each bay is 2' 0" to allow for installation and maintenance.

1.4 Compliance Information

- 1.4.1 **Safety Compliance:** This unit meets the requirements of UL 60950-1, Standard for Information Technology Equipment, and is UL Recognized as a power supply for use in Telephone, Electronic Data Processing or Information Processing Equipment. This unit meets the requirements of CAN/CSA 22.2, No. 60950-00 and is tested and Certified by UL ("c UR") as a Component Type Power Supply.
- 1.5 System Interface Board Ratings (List 61, 62, 63)
 - 1.5.1 Battery Fuse Alarm Input Rating
 - (A) The default is 400mV. Anything greater than 400mV causes alarm to be raised.
 - 1.5.2 Load Fuse Alarm Input Signal
 - (A) Anything greater than 19V causes alarm to be raised.
 - 1.5.3 Battery and Load Shunt Input Rating
 - (A) 1mV 150mV.
 - 1.5.4 LVD Sense Input Rating
 - (A) Normal state is at 60V or less. A RTN signal indicates the contactor is open.
 - 1.5.5 LVD Driver Output Rating
 - (A) Mono-stable, normal state is 60V or less at 1A continuous rating. Normally closed contactors are used for mono-stable option.
 - (B) Bi-Stable, normal state less than 60V and 2A at 500ms 1000ms pulse rating.
- 1.6 IB2 (Controller Interface Board) Ratings (List 61, 62, 63)
 - 1.6.1 Digital Input Ratings
 - (A) Maximum Voltage Rating: 60V DC.
 - (B) Active High: > 19V DC.
 - (C) Active Low: < 1V DC.
 - 1.6.2 Relay Ratings
 - (A) 1A Steady State @ 30V DC.
 - (B) 3A Peak @ 30V DC.
- 2. RECTIFIER SPECIFICATIONS

Refer to the separate Rectifier Instruction Document (UM1R483500E).

3. CONVERTER SPECIFICATIONS


Refer to the separate Converter Instruction Document (UM1C400483500E).

MECHANICAL SPECIFICATIONS

Overall Dimensions

Module Mounting Shelf (List 1, 3, and 11)

List 1 Shown.



0 1.484 0 2.250 1.484 Mounting

Mounting Angle Detail

Notes:

- All dimensions are in inches, unless otherwise specified.
- 2. Weight in LBS.
 Shelf
 Net: 17
 Shipping: 18
 Rectifier Module
 Net: 7
 Shipping: 8
- 3. Finish:

Shelf and Rectifier Module Bodies: Bright Zinc Plating (M500-53) Rectifier Module Face Plates: Textured Gray (M500-147)

 Mounting angles may be positioned from flush front mounting to 6-inch front projection mounting, in 1-inch increments.






Figure 12

Revision U, August 6, 2018

Module Mounting Shelf (List 22, 31, 32, 33, 41, and 42)

List 31 Shown.





Notes:

- 1. All dimensions are in inches, unless otherwise specified.
- 2. Weight in LBS. Shelf Net: 17
 - Shipping: 18 Rectifier/Converter Module
 - Net: 7 Shipping:8
- 3. Finish: Shelf and Module Bodies: Bright Zinc Plating Module Face Plates: **Textured Gray**
- 4. Mounting angles are positioned for a fixed 9-inch front projection mounting.





Figure 13

Module Mounting Shelf (List 21 and List 40)

List 21 Shown.



Notes:

- 1. All dimensions are in inches, unless otherwise specified.
- 2. Weight in LBS. Shelf Net: 17

Shipping: 18 Rectifier/Converter Module Net: 7

- Shipping: 8 3. Finish: Shelf and Module Bodies:
 - Bright Zinc Plating Module Face Plates: **Textured Gray**
- 4. Mounting angles are positioned for a fixed 9-inch front projection mounting.





Figure 14

Module Mounting Shelf (61, 62, and 63)

List 61 Shown.



Notes:

- 1. All dimensions are in inches, unless otherwise specified.
- 2. Weight in LBS.

Shelf

Net: 24

Shipping: 25

Rectifier Module

Net: 7

Shipping: 8

NCU Controller

Net: 2.2

Shipping: 3.2

3. Finish:


Angle Detail

Shelf and Rectifier Module Bodies:

Bright Zinc Plating
Rectifier Module Face Plates:


Textured Gray

4. Mounting angles are positioned for a fixed 6-inch front projection mounting.



Front View

Top View








Figure 15



Module Mounting Shelf (List 51, 52, and 53)

List 51 Shown.



Notes:

- 1. All dimensions are in inches, unless otherwise specified.
- 2. Weight in LBS.

Shelf

Net: 21

Shipping: 22

Rectifier Module

Net: 7

Shipping: 8

3. Finish:


Shelf and Rectifier Module Bodies:

Bright Zinc Plating


Rectifier Module Face Plates:


Textured Gray

4. Mounting angles are positioned for a fixed 6-inch front projection mounting.









RELATED DOCUMENTATION



Spec. No. 588705000 Module Mounting Shelf

Schematic Diagram:SD588705000Wiring Diagram:T588705000

Rectifiers (1R483200, 1R483200E, 1R483500E)

Rectifier User Instructions: UM1R483500E

Converters (1C400483500E)

Converter User Instructions: UM1C400483500E

Spec. No. 582126000 NetSure Power System

System Application Guide:SAG582126000System Installation Instructions:Section 5974System User Instructions:Section 5975Color MCA Menu Tree:Section 6022

Spec. No. 582126100 NetSure Power System

System Application Guide:SAG582126100System Installation Instructions:Section 6027System User Instructions:Section 6028Color MCA Menu Tree:Section 5886

Spec. No. 582127000 NetSure Power System

System Application Guide:SAG582127000System Installation Instructions:IM582127000System User Instructions:UM582127000NCU Controller Instructions:UM1M830BNA

Spec. No. 582127100 NetSure Power System

System Application Guide:SAG582127100System Installation and User Instructions:UM582127100NCU Controller Instructions:UM1M830BNA

REVISION RECORD



(ECO)	Description of Change	Date	Approved
LLP205300	New	05/17/2006	John Jasko
LLP207736	Miscellaneous updates per marketing.	01/11/2007	John Jasko
LLP207874	AC input terminal block changed. Wire size capacity updated.	05/04/2007	John Jasko
LLP208864	Revised aisle space clearance requirements in Specifications section. Corrected heat dissipation data in Para. 1.2.4 and 1.2.5.	07/30/2007	J. Kirkpatrick
LLP210447	Added List 3. Corrected input data. Removed input data for multiple rectifier modules.	05/16/2008	J. Kirkpatrick
LLP211072	List 11 (Shelf with AC Line Cords) added.	07/23/2008	John Jasko
LLP213309	1R483200e Rectifier Module added as option.	01/20/2010	Shanon Ravacio
LLP213967	Physical Dimension labeling updated.	05/06/2010	Shanon Ravacio
LLP214969	Added 1R483500e rectifier to the existing power system of 582126000. Added and updated charts for rectifier specifications.	01/04/2011	Khristebelle Ilagan
LLP215678	Correct wrong content of GBB rectifier fan replacement PNs.	06/13/2011	Khristebelle Ilagan
LLP215944	Adding compatibility information for 1R483500e rectifiers in systems with older software. Removing rectifier module specs. from this document and referencing the separate rectifier document.	08/11/2011	John Jasko
LLP216539	Lists 21, 22, 31, and 32 added. Shelf is now used with systems having the ACU+ Controller, document revised to talk about the controller in generic terms.	04/03/2012	John Jasko
LLP218430	Lists 51, 52, 53, 61, 62, and 63 added.	05/07/2013	John Jasko
LLP218889	Lists 40, 41, and 42 (C400/48-3500e) added.	09/12/2013	John Jasko
LLP220488	Updating DC input voltage range for converter 1C400483500e and 588705000 using it.	06/02/2014	John Jasko
LLP222051	Added a List option that will allow for 277v AC input.	09/03/2015	Mitch Emata
LLP223817	Rebranded Vertiv.	04/25/2017	John Jasko
LLP224154	Updates for program PWR00980N.	06/23/2017	John Jasko
LLP225149	Updates for program RRM105960S (replacing ACU+ with NCU).	08/06/2018	John Jasko Mike Smith Aug 16, 2018 John Jasko Aug 20, 2018
	LLP207736 LLP207874 LLP208864 LLP210447 LLP211072 LLP213309 LLP213967 LLP214969 LLP215678 LLP215944 LLP216539 LLP218430 LLP218889 LLP220488 LLP22051 LLP223817 LLP224154	LLP207736 Miscellaneous updates per marketing. LLP207874 AC input terminal block changed. Wire size capacity updated. Revised aisle space clearance requirements in Specifications section. Corrected heat dissipation data in Para. 1.2.4 and 1.2.5. LLP210447 Added List 3. Corrected input data. Removed input data for multiple rectifier modules. LLP211072 List 11 (Shelf with AC Line Cords) added. LLP213309 IR483200e Rectifier Module added as option. LLP213967 Physical Dimension labeling updated. Added 1R483500e rectifier to the existing power system of 582126000. Added and updated charts for rectifier specifications. LLP215678 Correct wrong content of GBB rectifier fan replacement PNs. Adding compatibility information for 1R483500e rectifiers in systems with older software. Removing rectifier module specs. from this document and referencing the ACU+ Controller, document revised to talk about the controller in generic terms. LLP218430 Lists 51, 52, 53, 61, 62, and 63 added. LLP218889 Lists 40, 41, and 42 (C400/48-3500e) added. LLP220488 Updating DC input voltage range for converter 1C400483500e and 588705000 using it. LLP223817 Rebranded Vertiv. LLP225149 Updates for program PWR00980N.	LLP20736 Miscellaneous updates per marketing. 01/11/2007 LLP207874 AC input terminal block changed. Wire size capacity updated. 05/04/2007 Revised aisle space clearance requirements in Specifications section. Corrected heat dissipation data in Para. 1.2.4 and 1.2.5. LLP210447 Added List 3. Corrected input data. Removed input data for multiple rectifier modules. 05/16/2008 LLP211072 List 11 (Shelf with AC Line Cords) added. 07/23/2008 LLP213309 1R483200e Rectifier Module added as option. 01/20/2010 LLP213967 Physical Dimension labeling updated. 05/06/2010 Added 1R483500e rectifier to the existing power system of 582126000. Added and updated charts for rectifier specifications. 06/13/2011 LLP215678 Correct wrong content of GBB rectifier fan replacement PNs. 06/13/2011 Adding compatibility information for 1R483500e rectifier module specs. from this document and referencing the separate rectifier document. 08/11/2011 LLP216539 Lists 21, 22, 31, and 32 added. Shelf is now used with systems having the ACU+ Controller, document revised to talk about the controller in generic terms. 04/03/2012 LLP218430 Lists 51, 52, 53, 61, 62, and 63 added. 05/07/2013 LLP218889 Lists 40, 41, and 42 (C400/48-3500e) added. 09/12/2013 LLP220488 Updating DC input voltage range for converter 1C400483500e and 588705000 using it. 06/02/2014 LLP223817 Rebranded Vertiv. 04/25/2017 LLP225149 Updates for program PWR00980N. 06/23/2017

VertivCo.com | Vertiv Headquarters, 1050 Dearborn Drive, Columbus, OH, 43085, USA

© 2018 Vertiv Co. All rights reserved. Vertiv and the Vertiv logo are trademarks or registered trademarks of Vertiv Co. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness of this document, Vertiv Group Corporation assumes no responsibility and disclaims all liability for damages resulting from use of this information or for any errors or omissions. Specifications are subject to change without notice.

